

MICRO SWITCHFREEPORT ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929**SWITCH - BASIC**CATALOG LISTING
BA-2RV2233T**ABS5680****BA-2RV2233T**
PAGE 1 OF 1**M**DRAWING
NUMBER

8

ISSUE

REPLACES

PR-5617

RELEASE NO.

CHECK

REVISIONS

A	CO-69351-D	JWB	18 JUL 91
B	CO-70184-G	GJW	7 MAR 92
C	CO-72387	JJD	1 MAY 92
D	CO-75204B	DAW	1 FEB 94
E	CO-77630	SAB	9 JUN 94
F	C093346	DLT	26 AUG 98
G	0018388	TGP	17 FEB 06

RJ

CHECK

RJ

CHECK

RJ

CHECK


RJ

CHECK

RJ


CHECK

RJ



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

**CHARACTERISTICS**

OPERATING FORCE ----- 6 OZ MAX

RELEASE FORCE ----- 1 1/2 OZ MIN

PRETRAVEL ----- .250 MAX

DIFFERENTIAL TRAVEL ----- .045 MAX

OVERTRAVEL ----- .030 MIN

ELECTRICAL DATACONTACT ARRANGEMENT
S P D T20A-125, 250 OR 480 VAC; 10A-125 VAC "L"
1HP-125 VAC; 2HP-250 VAC
CODE L23 1/2A-125 VDC; 1/4A-250 VDC

L288

L308

L315



20(3)A 250V ~ T85 5E4

SCALE

FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE:

DIM.	TOL.	DIM.	TOL.
mm	mm/in	in	mm/in
NO PLACES	X	1/64	
ONE PLACE	X,X	0.4/018	X,X 0.81/03
TWO PLACES	X,X,X	0.15/008	X,X,X 0.38/015
THREE PLACES	X,X,X,X		X,X,X,X 0.13/005

DESIGN UNITS ☐ SI METRIC☒ US CUSTOMARY

WEIGHT

FORMTEK

FO-52848-A

DRAWN

J A L 13 FEB 76