Part Number : 5602050103
Product Description : CTX-J 100 Female Crimp Terminal, Tin Plated, 0.75-1.25mm² Wire Size, Medium Grip, Sealed
Series Number : 560205
Status : Active
Product Category : Crimp Terminals
Engineering Part Number : 560205



Documents and Resources

Drawings

5602050103_sd.pdf

PK-560205-001-001.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

5601510002-CN-001.pdf

AS-560151-001-JP-001.pdf

5602050001-AS-CH-000.pdf

AS-560205-001-001.pdf

Tooling Specifications

ATS-638247700-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)

Downloaded from Arrow.com.

EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	560205
Description	CTX-J 100 Female Crimp Terminal, Tin Plated, 0.75-1.25mm^2 Wire Size, Medium Grip, Sealed
Application	Automotive, Signal, Wire-to-Board
Product Name	Compactus,CTX-J 100
UPC	191130052011

Electrical

Current - Maximum per Contact	6.0A
Voltage - Maximum	250V

Physical

Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin

Downloaded from Arrow.com.

Material - Plating Termination	Tin
Net Weight	0.264/g
Packaging Type	Reel
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	N/A
Wire Size (AWG)	N/A
Wire Size mm^2	0.75-1.25

Downloaded from Arrow.com.