




Part Number : [638130800](#)
Product Description : Manual Extraction Tool
Series Number : 207121
Status : Active
Product Category : Crimp Presses and Crimp Hand Tools



Documents & Resources

Tooling Specifications

- [ATS-638130800-001.pdf](#)
- [TM-638000029-001.pdf](#)
- [TM-638000029DE-001.pdf](#)
- [TM-638000029SP-001.pdf](#)
- [TM-638000029FR-001.pdf](#)
- [TM-638000029IT-001.pdf](#)
- [TM-638000029JP-001.pdf](#)
- [TM-638000029KR-001.pdf](#)
- [TM-638000029MY-001.pdf](#)
- [TM-638000029PL-001.pdf](#)
- [TM-638000029RU-001.pdf](#)
- [TM-638000029SK-001.pdf](#)
- [TM-638000029TH-001.pdf](#)
- [TM-638000029VN-001.pdf](#)
- [TM-638000029CN-001.pdf](#)
- [TM-638000029TW-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant

Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207121
Description	Manual Extraction Tool
Function	Extraction
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	N/A
Tool Type	Extraction Hand Tool
UPC	800754250429
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and

	sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.
--	---

Physical

Net Weight	1.000/g
------------	---------

Applicable Parts

Description	Part Number
Sabre Crimp Terminal, Male, 18 AWG, 3.30mm Max. Insulation Diameter, Reel Packaged, Unplated, Brass Contact	<u>431781001</u>
Sabre Crimp Terminal, Male, 18 AWG, 3.30mm Max. Insulation Diameter, Reel Packaged, Tin (Sn) Plated Brass Contact	<u>431781002</u>
Sabre Crimp Terminal, Male, Double 20+18 or Single 16-14 AWG, 3.60mm Max. Insulation Diameter, Reel Packaged, Unplated, Brass Contact	<u>431782001</u>
Sabre Crimp Terminal, Male, Double 20+18 or Single 16-14 AWG, 3.60mm Max. Insulation Diameter, Reel Packaged, Tin (Sn) Plated Brass Contact	<u>431782002</u>
Sabre Crimp Terminal, Male, Double 18+18 AWG, 4.57mm Max.	<u>431783001</u>

Insulation Diameter, Reel Packaged, Unplated, Brass Contact	
Sabre Crimp Terminal, Male, Double 18+18 AWG, 4.57mm Max. Insulation Diameter, Reel Packaged, Tin (Sn) Plated Brass Contact	<u>431783002</u>
Sabre Crimp Terminal, Male, 20-18 AWG, 2.50-2.85mm max. Insulation Diameter, Reel Packaged, Unplated, Brass Contact	<u>431784001</u>
Sabre Crimp Terminal, Male, 20-18 AWG, 2.50-2.85mm max. Insulation Diameter, Reel Packaged, Tin (Sn) Plated Brass Contact	<u>431784002</u>
Sabre Crimp Terminal, Male, 18 AWG, 3.30mm Max. Insulation Diameter, Reel Packaged, Tin (Sn) Plated Brass Contact, Last-Make Wipe Length, Complies with UL1977 Finger Proof Access Requirement	<u>431785002</u>
Sabre Crimp Terminal, Male, 16-14 AWG, 3.60mm Insulation Diameter, Reel Packaged, Tin (Sn) Plated Brass Contact, Last-Make Wipe Length, Complies with UL1977 Finger Proof Access Requirement	<u>431786002</u>
7.50mm Pitch Sabre Plug Crimp Housing, UL 94V-2, 2 Circuits, Natural	<u>436801002</u>
7.50mm Pitch Sabre Plug Crimp Housing, UL 94V-2, 3 Circuits, Natural	<u>436801003</u>
7.50mm Pitch Sabre Plug Crimp Housing, UL 94V-2, 4 Circuits, Natural	<u>436801004</u>
7.50mm Pitch Sabre Plug Crimp Housing, UL 94V-2, 5 Circuits, Natural	<u>436801005</u>
7.50mm Pitch Sabre Plug Crimp Housing, UL 94V-2, 6 Circuits, Natural	<u>436801006</u>

7.50mm Pitch Sabre Plug Crimp Housing, UL 94V-0, 2 Circuits, Black, Black	<u>436802002</u>
7.50mm Pitch Sabre Plug Crimp Housing, UL 94V-0, 3 Circuits, Black, Black	<u>436802003</u>
7.50mm Pitch Sabre Plug Crimp Housing, UL 94V-0, 4 Circuits, Black, Black	<u>436802004</u>
7.50mm Pitch Sabre Plug Crimp Housing, UL 94V-0, 5 Circuits, Black, Black	<u>436802005</u>
7.50mm Pitch Sabre Plug Crimp Housing, UL 94V-0, 6 Circuits, Black, Black	<u>436802006</u>
7.50mm Pitch Sabre Plug Housing, UL 94V-2, 2 Circuits, Glow-Wire Capable, Black	<u>436803002</u>
7.50mm Pitch Sabre Plug Housing, UL 94V-2, 3 Circuits, Glow-Wire Capable, Black	<u>436803003</u>
7.50mm Pitch Sabre Plug Housing, UL 94V-2, 4 Circuits, Glow-Wire Capable, Black	<u>436803004</u>
7.50mm Pitch Sabre Plug Housing, UL 94V-2, 5 Circuits, Glow-Wire Capable, Black	<u>436803005</u>
7.50mm Pitch Sabre Plug Housing, UL 94V-2, 6 Circuits, Glow-Wire Capable, Black	<u>436803006</u>

This document was generated on Sep 18, 2025