IPSLUAT series

Low Range, Intrinsically Safe Pressure Sensor

Approvals:-
ATEX / IECEx
II Ex ia IIC T4 Ga Ta (see schedule)



- ***Piezo-resistive sensor***
- ***Stainless steel body & diaphragm***
- ***Accuracy <±0.25% FS BFSL***
- ***Pressure ranges from 1psi to 15psi***
- ***Gauge or Absolute pressure reference***

The IPSLUAT is suitable for use in a wide range of applications in hazardous areas. The probe uses a piezo-resistive silicon sensor, giving excellent media compatibility within an oil filled 316L stainless steel housing

The electronics incorporate a microprocessor based amplifier, requiring no adjusting and giving stable electronics, especially in high vibration/shock applications.

Each device is temperature compensated, calibrated and supplied with a traceable serial number and calibration certificate.

There is a choice of internal O ring seals to ensure that the device is compatible with a wide range of media.

Performance

Accuracy (Non-Linearity & Hysteresis)		<±0.25% / FS (BFSL) for gauge, <±0.5% for Absolute
Setting Errors (offsets)	2-wire	Zero & Full Scale, <±0.5% / FS

Options available on the IPSLUAT pressure transmitter.

Pressure range
Pressure reference (G or Abs)

Material Specifications

Housing	316 Stainless Steel
"O" ring seals	Viton
Diaphragm	316L Stainless Steel
Media wetted parts	Housing & connection, "O" ring seal, diaphragm

Miscellaneous

Weight	Approx 100g
Installation position	Any, small zero shift when tilted through 90°
Operational Life	> 100x 10^6 cycles
Insulation resistance	> 50MOhms at 50Vdc

Electrical Protection

Supply reverse polarity	No damage/no function
Electromagnetic compatibility	CE Compliant

Mechanical Stability

Shock	100g / 11s
Vibration	10g RMS (20 - 2000Hz)

Environment & Thermal Effects

Media Temperature	-20°C to +120°C
Storage temperature	-40°C to +110°C
Compensated temperature range	+20°C to +80°C
Thermal Zero Shift (TZS)	<±0.04% /FS/°C
Thermal Span Shift	<-0.015% /°C
Permissible environment zone 0	-20°C to +60°C with patm 0.8 to 1.1 bar

Cynergy3 Components Ltd.
7 Cobham Road
Ferndown Industrial Estate
Wimborne, Dorset BH21 7PE
Telephone +44 (0) 1202 897969
Email:sales@cynergy3.com

IPSLUAT 2016

ISO9001 CERTIFIED

Made in the UK

www.cynergy3.com

© 2016 Cynergy3 Components, All Rights Reserved. Specifications are subject to change without prior notice. Cynergy3 Components and the Cynergy3 Components logo are trademarks of Cynergy3 Components Limited.

Downloaded from Arrow.com.

IPSLUAT series


Low Range, Intrinsically Safe Pressure Sensor

Pressure Ranges							
Nominal Pressure, Gauge,	psi	0.75	1.5	3.75	7.5	11.25	15
Nominal Pressure, Absolute	psi				7.5	11.25	15
Permissible Overpressure	psi	30	30	30	75	75	75

Output Signal and Supply Voltage			DIN 43650	
Wire system	Output	Supply Volts	Connection	Pin No.
2-wire	4-20mA	10-28Vdc	+ve Supply	Pin 1
			-ve Supply	Pin 2
			Ground	Earth pin

Part Number	Pressure Rating
IPSLUAT-GP001-5	0 - 1psi G
IPSLUAT-GP002-5	0 - 2psi G
IPSLUAT-GP005-5	0 - 5psi G
IPSLUAT-GP008-5	0 - 8psi G
IPSLUAT-GP010-5	0 - 10psi G
IPSLUAT-GP015-5	0 - 15psi G
IPSLUAT-AP005-5	0 - 5psi Abs
IPSLUAT-AP010-5	0 - 10psi Abs
IPSLUAT-AP015-5	0 - 15psi Abs

Mechanical Dimensions



ISO9001 CERTIFIED

Made in the UK

www.cynergy3.com

© 2016 Cynergy3 Components, All Rights Reserved. Specifications are subject to change without prior notice. Cynergy3 Components and the Cynergy3 Components logo are trademarks of Cynergy3 Components Limited.

Downloaded from Arrow.com.