



ReSpeaker USB Mic Array

SKU 107990193



Plug&Play Far-field microphone array for your application! Not a bare dev board, but an out-of-the-box device.

- 1 +

CN Warehouse



Add to Cart

Tags:

ReSpeaker

Mic Array

DOA

AEC

AGC

NS

Description

Documents

Images

Reviews

FAQs

An out-of-the-box voice pick-up device is the voice of the customer.

During the past year, [Respeaker Mic Array V2.0](#) has been sold out for more than 10K units in the format of the development board. Customers keep requesting a complete device with an enclosure, which is challenging for them to design it, considering the acoustic principles.

And here Seeed provides the answer with ReSpeaker USB Mic Array.

- An out-of-box device with a well-designed acoustic structure brings the flexibility for the customer to build in their solution.
- Mold injected enclosure available, saves the time to go to the market and the mold cost.

The difference between the PCBA inside ReSpeaker USB Mic Array and Respeaker Mic Array V2.0:

- Optimized power circuit
- Move the audio jack and micro USB port to the backside.

Applicable Scenario

- Microphone device in the meeting room: Used as a microphone device in the meeting room for 5~6 attendees.
- Smart home: Snips demo to turn on/off a light;
- Device automation: Snips command on a coffee machine

Features

- Plug & Play (No driver required), compatible with Windows 10/8/7, Mac, Linux and Android that support OTG.
- Voice Pick-up device, Far-field voice pick-up up to 5m and supports 360° pick-up pattern
- Acoustic algorithms implemented
- DOA(Direction of Arrival).
- AEC(Automatic Echo Cancellation),
- AGC(Automatic Gain Control),
- NS(Voice Suppression)
- Built-in audio jack, which allows for plugging in headphones or speakers (speaker not included)

Applications

- Voice pick-up device
- Home/Office automation device
- In-car voice assistant
- Healthcare device
- Voice interaction robot
- Other applications



Compatibility

When it comes to development we believe you should have as many options as possible. The ReSpeaker USB Mic Array is able to work with most modern Linux, macOS, and Windows systems*.

Compatible with



*We do recommend Linux for firmware updates.



Setup, Documentation, and Support

We are working hard to ensure the setup is simple. The documentation on our [wiki](#) will help you get up and running quickly, and should unknown issues pop up our tech support team is ready to help. You can ask questions in our [ReSpeaker forum](#), which is checked daily. You can also check out the [GitHub](#) for more support.



Technical Specifications

- XVF-3000 from XMOS
- 4 High Performance Digital Microphones
- Supports Far-field Voice Capture
- Speech Algorithms On-Chip
- 12 Programmable RGB LED Indicators
- Microphones: ST MP34DT01TR-M
- Sensitivity: -26 dBFS (Omnidirectional)
- Acoustic Overload Point: 120 dB SPL
- SNR: 63 dB
- Power Supply: 5V DC from Micro USB or Expansion Header
- Dimensions: 70mm (Diameter)
- 3.5mm Audio Jack Output Socket

Technical Details

Dimensions

77mm (Diameter)

Weight (N/W)

43.6g

Weight (G.W.)	104.2g
Battery	Exclude
Part List	
ReSpeaker USB Mic Array	1
USB Type A to Micro USB cable	1
Instruction Card	1

ECCN/HTS

HSCODE	8518900090
UPC	

Company

Official Website
About Seeed
Solution
Distributors
Careers
Contacts

Help Center

How to Get Help
FAQ
Technical Support
Shipping & Order
Warranty & Returns
Payment Information

Community

Project Hub
Forum
Blog
Wiki

Stay Tuned

Enter Email Address

>

