





2 Poles

Technical data

- 1.Nominal voltage: 150V/4A
PITCH:2.5mm
- 2.Connection capacity:
AWG 28-20
- 3.Insulation Withstanding Voltage:
AC 1300V/MIN
- 4.Insulation Resistance:
1000MΩ or more at DC500V
- 5.Stripping length: 7-8mm
- 6.Operating temperature range:-40°C ~ 115°C
- 7.Undimensioned Tolerances:

Dim.L=(P-1)x2.5+3.1		
Dim.B=(P-1)x2.5		
P= number of poles		
0-30mm	±0.15	±0.20
over 30mm-60mm	±0.20	±0.25
over 60mm-90mm	±0.25	±0.30
over 90mm	±0.30	±0.40

8.Safety approval:

9.RoHS Compliance

Part No.:

OSTHWXXB050

No. of Poles	COLOR
02 2 Poles	0: Black
03 3 Poles	2: Red
...	3: Orange
24 24 Poles	4: Yellow
	5: Green (Standard)
	6: Blue
	8: Grey

Nonstandard colors
Mins could apply

5	SPRING	Stainless steel		P
4	CONTACT	BRONZE (PhBz)	TIN PLATED	P
3	LEVEL	PBT UL94V-0	ORANGE	P
2	COVER	PA66 UL94V-0	ALL COLOR	1
1	HOUSING	PA66 UL94V-0	ALL COLOR	1
ITEM	NAME OF PART	MATERIAL	NOTES	Q"TY
DWG	WF. Zhang	DATE 2017.10.31	UNITS: MM	SHEET: 1 OF 1
CHK.	WF. Zhang	DATE 2017.10.31	SCALE: NONE 2.5:1 (:)	REV.: A
APP.		DATE	TITLE: OSTHW Series 2.50mm Without flange type	X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°
			PART NO. OSTHWXXB050	
			DWG NO. OSTHWXXB050.dwg	

ON-SHORE TECHNOLOGY, INC.

△	DESCRIPTION	CHK.	DATE
SIGN			