



Part Number : [190080027](#)
Product Description : Flag Krimptite Quick Disconnect, Female, for 14-16 (2.00-1.30mm²) Wire, Mylar Tape, Tab 6.35 x 0.81mm
Series Number : 19008
Status : Active
Product Category : Quick Disconnects
Engineering Number : BB-1159T



Documents & Resources

Drawings

[190080027 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[PS-19902-005-001.pdf](#)

[PS-19902-015-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19008
Description	Flag Krimptite Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Mylar Tape, Tab 6.35 x 0.81mm
Product Name	Krimptite
Type	Flag Terminal
UPC	800753032651

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	Per Wire Specification
-------------------	------------------------

Physical

Barrel Type	Closed
Gender	Female
Glow-Wire Capable	No

Insulated	No
Insulation	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.741/g
Orientation	Flag
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Polarized to Mating Part	No
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	Per Wire Specification
Termination Interface Style	Crimp or Compression
Wire Size (AWG)	14, 16
Wire Size mm ²	1.30-2.00

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>190270085</u>
Mini-Mac Air Feed Mylar Tape Applicator	<u>638859000</u>

This document was generated on Sep 30, 2025