



Automotive Parts > Automotive Connectors > Automotive Housings > 48V Ready Mixed (Signal and Power) Connectors



Connector & Housing Type: **Housing for Female Terminals**

Number of Positions: **15**

Sealable: **Yes**

Operating Temperature Range: **-40 – 140 °C [-40 – 284 °F]**

Number of Rows: **2**

[All 48V Ready Mixed \(Signal and Power\) Connectors \(10\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	Yes
Connector Shape	Rectangular
Connector & Housing Type	Housing for Female Terminals
Sealable	Yes
Primary Locking Feature	On the Terminal
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	15
Number of Rows	2

Electrical Characteristics

Operating Voltage	60 VDC
-------------------	--------



Nominal Voltage Architecture

12 V, 24 V, 42 V, 60 V

Body Features

Cable Exit Angle	180°, 90°
Primary Product Color	Black
Connector & Keying Code	A

Contact Features

Contact Size	1.5K, 2.8mm
Contact Type	Receptacle
Mating Tab Width	1.5 mm, 2.8 mm [.059 in] [.11 in]
Contact Current Rating (Max)	40 A

Mechanical Attachment

Strain Relief	Without
Terminal Position Assurance	No
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PBT GF30
Centerline (Pitch)	4 mm, 6 mm [.157 in] [.236 in]

Dimensions

Product Width	25.7 mm [1.012 in]
Product Length	67.2 mm [2.646 in]
Connector Height	31.25 mm [1.23 in]

Usage Conditions

Operating Temperature Range	-40 – 140 °C [-40 – 284 °F]
Operating Temperature (Max)	140 °C [284 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

IP Rating	IP67
UL Flammability Rating	UL 94V-0

Packaging Features



Packaging Method	Box
Packaging Quantity	230

Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2112303-1
PROTECTION CAP, FOR REC.HSG GROUP E



TE Part # 964972-1
EINZELLEITERDICTNG



TE Part # 1-2378191-1
15POS, HYBRID, HDR ASSY, 180DEG, COD A



TE Part # CAT-AM705-T273
AMP MCP, RECEPTACLE AND TAB



TE Part # 3-1579018-8
UNLOCK TOOL



TE Part # 828905-1
SINGLE-WIRE-SEAL(5MM HOLE)



TE Part # CAT-H3399-B128
Heavy Duty Sealed Connector Series Backshells




TE Part # 1-1564530-1
15POS, MIXED, TAB HSG, ASSY



TE Part # 1-1564532-1
15POS, MIXED, TAB HSG, ASSY

Also in the Series | **Heavy Duty Sealed Connector Series**



Automotive Housings(215)



Automotive Seals & Cavity Plugs(5)



Data Connectivity Headers(18)

Customers Also Bought




TE Part #K1127520
Battery Disconnect 35-213-151-R-900



TE Part #284798-1
CRIMPED TAB CONTACT, P.C.B. INTERFACE



TE Part #1-968855-1
AMP MCP 2.8, CONTACT SWS



TE Part #1534099-1
MQS COVER 2X10P





TE Part #2-1563878-1
15POS, MIXED,REC HSG,SEALED, ASSY



TE Part #2137358-1
AMP-MCP 2.8mm RECEPTACLE HOUSING , 18POS

TE Part #044391-000
222K163-15/86-0

TE Part #2311056-2
48POS,MCON 1.2,REC HSG,SLD



TE Part #2329592-2
20POS,MQS,REC HSG,UNSLD

TE Part #9-1904049-3
V23134A1007X940-EV-850

Documents

Product Drawings

15POS, MIXED,REC HSG,SEALED,AS

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-1563878-1_J.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1563878-1_J.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1563878-1_J.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Heavy Duty Sealed Connector Series

English

HDSCS Catalog

English

ICT Terminals and Connectors Catalogue

English

CONNECTOR SELECTOR

English



Product Specifications

Heavy Duty Sealed Connector Series 2 to 18 Positions for AMP MCP* Contact Systems

English