



REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	--	RELEASED DRAWING	Dec-26-2016	Ben	Tommy



- NOTES : (UNLESS OTHERWISE SPECIFIED)
- MATERIAL :
SHELL : THERMOPLASTIC , UL94 V-0.
SEAL GASKET : NBR OR SR.
 - SPECIFICATIONS :
2.1 OPERATING TEMPERATURE : SEE TABLE.
2.2 INSULATION RESISTANCE : 5000 MEGOHMS MIN.
2.3 IP CLASS : IP67.
2.4 MATING CYCLES DURABILITY : 500 CYCLES MIN.
2.5 RoHS COMPLIANT.
 - ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.



KEY	PART NUMBER	
	-40°C ~ 105°C	-40°C ~ 125°C
N	RTS616*DCG	RTS616*DCG03

QUANTITY		PART NUMBER		DESCRIPTION		ITEM	
MATERIALS LIST							
UNLESS OTHERWISE SPECIFIED		SIGNATURES		DATE		Amphenol Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036	
1) All dimensions are in metric(mm).		DRAWN: Ben		Dec-26-2016			
2) Tolerances are as follows:		CHECKED:					
1 PL DEC ±0.30		ENGINEER:					
2 PL DEC ±0.15		APPROVAL:					
3 PL DEC ±0.08		CUSTOMER:				ECO-MATE,PLUG SEALING CAP,SIZE 16 SIZE: B TYPE: C- DWG NO: RTS616*DCG* REVISION: A1 SCALE: NONE SHEET 1 OF 1	
3) Note reference = 		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.					
MATERIAL SPECIFICATIONS:							
PROCESS SPECIFICATIONS:							
NEXT ASSY:							

TITLE: ECO-MATE,PLUG SEALING CAP,SIZE 16
DWG NO: RTS616*DCG*
REV: A1
SH: 1
OF: 1