
051-0318-0001 Product Details

Live Product Chat



051-0318-0001
(1466301-1)
TE Part Number: 1466301-1
Active
Add to Part List

SMB RF Connectors

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector
- Jack
- Miniature
- Terminate To Coaxial Cable
- Coupler Style = Threaded

View all Features | Find Similar Products

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Documentation & Additional Information

Product Drawings:
- BULKHEAD RECEPTACLE S-50 OHM TURRET 'D' MOUNT W/ WIR... (PDF, English)

Catalog Pages/Data Sheets:
- None Available

Product Specifications:
- None Available

Application Specifications:
- None Available

Instruction Sheets:
- None Available

CAD Files:
- None Available

List all Documents

Additional Information:
- Product Line Information

Related Products:
- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:
- Product Type = Connector
- Gender = Jack
- Connector Series = Miniature
- Body Style = Straight
- Grade = Commercial
- Safety Wire Holes = With
- Thread Size = 4.83 [.190]-32
- Panel Thickness (mm [in]) = 4.06 [0.160]
- Body Material = Brass
- Dielectric Material = TEFLON

Mechanical Attachment:
- Panel Attachment = With
- Panel Attachment Style = Front Mount
- Panel Attachment Method = Jam Nut

Electrical Characteristics:
- Connector Impedance (Ω) = 50
- Safety Wire Dia., Max. (mm [in]) = 0.35 [0.014]
- Environmental Seal = Without
- Solderless = No

Termination Related Features:
- Coaxial Cable Termination Type = Solder

Body Related Features:
- Coupler Style = Threaded
- Pin Protection = Without
- Solder Lug = With
- Body Plating = Silver
- Terminal Style = Turret Pin

Contact Related Features:
- Center Contact Plating = Gold
- Contacts = With

Industry Standards:
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260° C, Wave solder capable to 265°C, Reflow solder capable to 245°C, Reflow solder capable to 260°C, Pin-in-Paste capable to 245°C, Pin-in-Paste capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:
- Terminate To = Coaxial Cable

Other:
- Brand = Microdot

© 2008 Tyco Electronics Corporation All Rights Reserved

Downloaded from Arrow.com.