

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT — By — ALL RIGHTS RESERVED.

LOC

GP

DIST

00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

A — STRAIGHT PINS

PIN 1

3.18±.76
(.125±.030)

B — RIGHT ANGLE PINS
(BENT DOWN)

PIN 1

.5(.020)

3.18±.76
(.125±.030)

R.5(.020)
MIN.

C — RIGHT ANGLE STAGGERED PINS
(PIN 1 SHORT, BENT DOWN)

PIN 1

.5(.020)

3.18±.76
(.125±.030)

R.5(.020)
MIN.

2.54±.26
[.100±.010]

DIM "B"

D — STRAIGHT ANGLE STAGGERED PINS
(PIN 1 STRAIGHT)

PIN 1

.5(.020)

3.18±.76
(.125±.030)

R.5(.020)
MIN.

2.54±.26
(.100±.010)

DIM "B"

STANDARD JUMPERS
SMART DESCRIPTION

AUTOMOTIVE USE ONLY

FLEXSTRIP PRODUCT CODE

INSULATION MATERIAL:
N — NOMEX®
P — POLYESTER
T — TEFLON®
K — KAPTON®

CONDUCTOR PITCH:
1 — 1.27(.050)
2 — 2.54(.100)
3 — 3.18(.125)
4 — 3.81(.150)
5 — 5.08(.200)
6 — 1.90(.075)
7 — 2.00(.078)
8 — 1.25(.049)
9 — 1.00(.039)

FS N — 1 2 A — 70

PIN ARRANGEMENT
(FOR BOTH ENDS)
A THRU Z

INSULATION LENGTH IN INCHES
.50 MIN. — 30.0 MAX.
IN .100 INCREMENTS PLUS,
.25 AND .75

NUMBER OF CONDUCTORS

MANUFACTURING NOTE:

MINIMUM GAP BETWEEN STRIPS

SK/A/Z	.75 INCH
LP	1.1 INCH

MINIMUM CONDUCTOR COUNT
PER STRIP FOR LINE JOBS

PITCH	CONDUCTOR
1 1.27 (.050)	60
2 2.54 (.100)	60
3 3.18 (.125)	60
4 3.81 (.150)	50
5 5.08 (.200)	40
6 1.91 (.075)	60
7 2.0 (.078)	60
8 1.24 (.049)	60
9 1.0 (.039)	80

STANDARD LINE JOBS

FLEX STRIP

MATERIAL:
N — NOMEX®
P — POLYESTER
T — TEFLON®
K — KAPTON®

CONDUCTOR PITCH:
1 — 1.27(.050)
2 — 2.54(.100)
3 — 3.18(.125)
4 — 3.81(.150)
5 — 5.08(.200)
6 — 1.90(.075)
7 — 2.00(.078)
8 — 1.25(.049)
9 — 1.00(.039)

THE FOLLOWING ORDERING CODE IS A SPECIAL FOR TE CONNECTIVITY GERMANY
DESCRIBING A STRIP OF ANY INSULATION MATERIAL, ANY PITCH
AND ANY INSULATION LENGTH WITH A 11.00[.433] MIN
PIN LENGTH UNLESS OTHERWISE SPECIFIED:—

FS X—X X J—A A W

FS N 1 — 2 SK (LP)

LONG PIN (OPTIONAL)

LINE JOB DESIGNATOR (SK, A, Z)

INSULATION LENGTH IN INCHES
.5 MIN. — 30.0 MAX.
IN .100 INCREMENTS,
PLUS .25 & .75

Nomex®, Teflon® and Kapton® are trademarks of E. I. DuPont de Nemours.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± —
4 PLC ± —
ANGLES ± 1/2°
FINISH —

DWN

J. SCHWARTZ

28FEB01

CHK

E. FOX

28FEB01

APVD

E. FOX

28FEB01

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

—

CUSTOMER DRAWING

TE Connectivity

NAME

FLEXSTRIP PIN CONFIGURATIONS, GENERIC

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

—

SCALE

N.T.S.

SHEET

2 OF 4

REV

H1

1470-19 (3/11)

Downloaded from Arrow.com

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

GP

00

—

SEE SHEET 1

—

—

—

NORMAL CONDUCTOR PITCH		1.00 (.039)	1.25 (.049)	1.27 (.050)	1.90 (.075)	2.00 (.078)	2.54 (.100)	3.18 (.125)	3.81 (.150)	5.08 (.200)
WIRE GAUGE		AWG 28	AWG 28	AWG 28	AWG 26	AWG 26	AWG 24	AWG 24	AWG 24	AWG 24
NOMINAL WIRE DIAMETER		.32(.0126)	.32(.0126)	.32(.0126)	.40(.0159)	.40(.0159)	.51(.0201)	.51(.0201)	.51(.0201)	.51(.0201)
CURRENT RATING		8	8	8	8	8	8	8	8	8
VOLTAGE RATING		8	8	8	8	8	8	8	8	8
MAX NUMBER OF CONDUCTORS PER JUMPER		8	8	8	8	8	8	8	8	8
MIN BREAKDOWN VOLTAGE @ 1 MIN		8	8	8	8	8	8	8	8	8
INSULATION RESISTANCE (GND. SIG. GND) 305 (12") SAMPLE @ 500VDC	P N T K	8	8	8	8	8	8	8	8	8
CAPACITANCE (pf / 50.8 (12") LENGTH) (GND, SIG, GND) (AVERAGE)	P N T K	8	8	8	8	8	8	8	8	8
CHARACTERISTIC IMPEDANCE (GND. SIG. GND) (AVERAGE)	P N T K	8	8	8	8	8	8	8	8	8
APPLICATION TEMP RANGE (C°) (FOR SOLDERING)	P N T K	200 / 4 sec 200 / 4 sec 240 / 4 sec 240 / 4 sec	200 / 4 sec 200 / 4 sec 240 / 4 sec 240 / 4 sec	200 / 4 sec 200 / 4 sec 240 / 4 sec 240 / 4 sec	200 / 4 sec 200 / 4 sec 240 / 4 sec 240 / 4 sec	200 / 4 sec 200 / 4 sec 240 / 4 sec 240 / 4 sec	250 / 4 sec 250 / 4 sec 260 / 5 sec 260 / 5 sec	250 / 4 sec 250 / 4 sec 260 / 5 sec 260 / 5 sec	250 / 4 sec 250 / 4 sec 260 / 5 sec 260 / 5 sec	250 / 4 sec 250 / 4 sec 260 / 5 sec 260 / 5 sec
OPERATING TEMPERATURE (C°) 11	P N T K	-40 to 105 (For all Conductor Pitches) -40 to 125 (For all Conductor Pitches) -40 to 150 (For all Conductor Pitches) -40 to 150 (For all Conductor Pitches)								
MINIMUM BEND RADIUS 7	P N T K	3.18mm (For all Conductor Pitches) 3.18mm (For all Conductor Pitches) 3.18mm (For all Conductor Pitches) 3.18mm (For all Conductor Pitches)								
UL STYLE NUMBER	P N T K	2639 (For all Conductor Pitches .100 and above) 5456 (For all Conductor Pitches .100 and above) 2928 (For all Conductor Pitches .100 and above) 2927 (For all Conductor Pitches .100 and above)								

ABR.	MATERIAL	SPECIFICATION
	COPPER WIRE	100-1577
P	POLYESTER	100-1575
N	NOMEX®	100-1758
T	TEFLON®	100-1574
K	KAPTON®	100-1576

Nomex®, Teflon® and Kapton® are trademarks of E. I. DuPont de Nemours.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± 1/2°

MATERIAL

-

FINISH

-

DWN
J. SCHWARTZ
28FEB01

CHK
E. FOX
28FEB01

APVD
E. FOX
28FEB01

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
FLEXSTRIP PIN CONFIGURATIONS, GENERIC

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1474339

RESTRICTED TO
-

SCALE
N.T.S.

SHEET
4 OF 4

REV
H1

1470-19 (3/11)

Downloaded from Arrow.com