


MALE PCB PINS

PRINTED CIRCUIT PINS

0259/0286/1941

XXXX-0-00-XX-00-00-03-0


Press-fit in .057/.059 mounting hole



2956-0

2956-0-00-XX-00-00-03-0


Surface mount



2956-1

2956-1-00-XX-00-00-03-0


Surface mount



4956-1

4956-1-00-XX-00-00-33-0


Surface mount



8876

8876-0-00-XX-00-00-03-0


Press-fit in .057 mounting hole



1938

1938-0-00-XX-00-00-03-0


Press-fit in .057 mounting hole



1940

1940-0-00-XX-00-00-03-0


Press-fit in .057 mounting hole



1942

1942-0-00-XX-00-00-03-0


Press-fit in .057 mounting hole



3024

3024-0-01-XX-00-00-03-0


Press-fit in .057 mounting hole



1107

1107-0-01-15-00-00-03-0


Press-fit in .057 mounting hole



3000

3000-0-00-XX-00-00-03-0

Press-fit in .061 mounting hole. Accepts wire sizes 24 AWG Max. / 28 AWG Min.



SPECIFICATIONS:

Pin Material: Brass Alloy 360, 1/2 Hard
(Except swage pins which are annealed)

Dimensions: Inches

Tolerances On: Lengths: $\pm .005$
Diameters: $\pm .002$
Angles: $\pm 2^\circ$

RoHS-2
2011/65/EU

ORDER CODE: XXXX - X - 0X - XX - 00 - 00 - XX - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 200 μ " TIN/LEAD OVER NICKEL
- 80 200 μ " TIN OVER NICKEL (RoHS)
- 15 10 μ " GOLD OVER NICKEL (RoHS)
- 21 20 μ " GOLD OVER NICKEL (RoHS)
- 34 50 μ " GOLD OVER NICKEL (RoHS)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com