

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

BZ-2RQ181-D5

BZ-2RQ181-D5

PAGE 1 OF 1

M

DRAWING
NUMBER

7

ISSUE

REPLACES

RELEASE NO. PR-11614

CHECK

REVISIONS

A	CO-58037	SMA	1 OCT 85
B	CO-77591	DAW	22 JUN 94
C	CO-77426-B	DLT	29 JUN 94
D	CO-82133	CSL	2 AUG 96
E	CO93346	DLT	10 SEP 98
F	CO-94212-C	DLT	17 SEP 99

CHECK

25 OCT 82

25 OCT 82

25 OCT 82

25 OCT 82

25 OCT 82

25 OCT 82

25 OCT 82

25 OCT 82

25 OCT 82

25 OCT 82

25 OCT 82

25 OCT 82

25 OCT 82


FORMTEK

FO-52848-A

DRAWN

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE ----- 9-13 OZ
RELEASE FORCE ----- 4 OZ MIN
DIFFERENTIAL TRAVEL --.0004 - .0020
OVERTRAVEL ----- .141 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

CODE L96 15A-125, 250 OR 480 VAC
1/8 HP-125 VAC; 1/4 HP-250 VAC
1/2 A-125 VDC; 1/4 A-250 VDC

L288
L299
L306

CE D A S

16A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

DIM.	TOL.	DIM.	TOL.
mm	mm/in	in	mm/in
NO PLACES	X	1/64	
ONE PLACE	X,X	0.4/018	X X
TWO PLACES	X,X,X	0.157/006	X X X
THREE PLACES	X,X,X,X		X X X X
ANGLES			

DESIGN UNITS

SI METRIC

U.S. CUSTOMARY

WEIGHT .107 LB

NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000±.002 CENTERS
- 2 HARDWARE FURNISHED UNASSEMBLED