

# RAD-CAB-EF393-10M - Antenna cable



2867665

<https://www.phoenixcontact.com/us/products/2867665>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Antenna cable, outside diameter: 10 mm (0.4 in.), inner conductor: stranded, attenuation: 2.9 / 5.6 / 9.9 dB at 0.9 / 2.4 / 5.8 GHz, connection: 2 x N (male), cable length: 10 m (32 ft.)



## Your advantages

- Halogen-free
- Easy installation, thanks to flexible inner conductor
- Flame-retardant
- Oil-resistant
- UV resistant
- For outdoor installation

## Commercial data

Item number	2867665
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN23
Product key	DNN2Z1
Catalog page	Page 391 (C-6-2019)
GTIN	4017918939038
Weight per piece (including packing)	1,760 g
Weight per piece (excluding packing)	1,800 g
Customs tariff number	85442000
Country of origin	PL

# RAD-CAB-EF393-10M - Antenna cable



2867665

<https://www.phoenixcontact.com/us/products/2867665>

## Technical data

### Product properties

Product type	Coaxial cable
--------------	---------------

### Electrical properties

Frequency range	0.3 GHz ... 6 GHz
Impedance	50 $\Omega$

### Connection data

#### Connector connection

Connection method	N (male)
Notes	Both sides
Connection method	N (male)

### Material specifications

Outer sheath, material	RADOX <sup>®</sup> (LSFH)
------------------------	---------------------------

### Cable/line

Cable length	10 m
Cable type	EF 393
External cable diameter	10.00 mm
Outer sheath, material	RADOX <sup>®</sup> (LSFH)
External sheath, color	black
Bending radius, long-term	50.00 mm
868 / 900 MHz	~ 2.9 dB (Attenuation of entire cable)
2.4 GHz	~ 5.6 dB (Attenuation of entire cable)
5.8 GHz	~ 9.9 dB (Attenuation of entire cable)
Resistance to oil	very good oil and chemical resistance

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
Ambient temperature (storage/transport)	-40 °C ... 105 °C
Ambient temperature (assembly)	-20 °C ... 60 °C
Resistance to oil	very good oil and chemical resistance

### Approvals

#### CE

Certificate	CE-compliant
-------------	--------------

### Standards and regulations

Resistance to oil	very good oil and chemical resistance
-------------------	---------------------------------------

# RAD-CAB-EF393-10M - Antenna cable



2867665

<https://www.phoenixcontact.com/us/products/2867665>

Standard designation	Flame retardancy
Standards/specifications	DIN EN 60332-1-2
	UL 1581
Standard designation	Halogen-free
Standards/specifications	IEC 60754
Standard designation	UV resistance
Standards/specifications	IEC 60068-2-5

## Mounting

Assembly instructions	Outdoors and indoors
-----------------------	----------------------

# RAD-CAB-EF393-10M - Antenna cable



2867665

<https://www.phoenixcontact.com/us/products/2867665>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2867665>



**EAC**

Approval ID: 19060508

# RAD-CAB-EF393-10M - Antenna cable



2867665

<https://www.phoenixcontact.com/us/products/2867665>

## Classifications

### ECLASS

ECLASS-11.0	27060310
ECLASS-12.0	27060310
ECLASS-13.0	27060310

### ETIM

ETIM 9.0	EC001682
----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# RAD-CAB-EF393-10M - Antenna cable



2867665

<https://www.phoenixcontact.com/us/products/2867665>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	56c2f959-3c8f-47a8-8c88-0f1157ea4ec8

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)