



SHEET 1 OF 1




P.C.B. LAYOUT








▲ CIRCUIT: SPST





NOTES:
1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
   X.XX=±0.25
3. RATING: 50mA @ 12VDC
4. TRAVEL: 0.25 +0.2/0.1mm
▲5. OPERATING FORCE: 160±50gf
6. CONTACT RESISTANCE: 100 Milli-Ohms Max
▲7. SHORTER LEAD (WITH COLOR) IS NEGATIVE (CATHODE).
▲8. LED: YELLOW
9. ▲ DENOTES CRITICAL PARAMETER

▲

LED SPECS	UNITS	YELLOW
FORWARD CURRENT	mA	10
FORWARD VOLTAGE	V	2.5
LUMINOUS INTENSITY	MCD	60

REV	ECO NO	DESCRIPTION	DATE	BY
E	ECO-101715	PRINT UPDATE	04/04/23	JS

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

E·SWITCH®

OBJECT ID 000017773

TITLE TL1240YQ

SCALE	DATE	DR	DWG	REV
4:1	7/20/2001	CJB	P010363	E

Downloaded from Arrow.com.