

MOSFET – N-Channel, UltraFET Trench

200 V, 9.5 A, 200 mΩ

FDMC2610

General Description

This N-Channel MOSFET is a rugged gate version of onsemi's advanced POWERTRENCH® process. It has been optimized for power management applications.

Features

- Max $R_{DS(on)} = 200 \text{ mΩ}$ at $V_{GS} = 10 \text{ V}$, $I_D = 2.2 \text{ A}$
- Max $R_{DS(on)} = 215 \text{ mΩ}$ at $V_{GS} = 6 \text{ V}$, $I_D = 1.5 \text{ A}$
- Low Profile – 1 mm Max in a Power 33
- Pb-Free, Halide Free and RoHS Compliant

Applications

- DC-DC Conversion

MOSFET MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ unless otherwise noted)


Symbol	Parameter	Value	Unit
V_{DS}	Drain to Source Voltage	200	V
V_{GS}	Gate to Source Voltage	± 20	V
I_D	Drain Current: Continuous (Silicon limited) $T_C = 25^\circ\text{C}$ Continuous (Note 1a) $T_A = 25^\circ\text{C}$ Pulsed	9.5 2.2 15	A
E_{AS}	Single Pulse Avalanche Energy (Note 3)	6	mJ
P_D	Power Dissipation: $T_C = 25^\circ\text{C}$ $T_A = 25^\circ\text{C}$ (Note 1a)	42 2.1	W
T_J, T_{STG}	Operating and Storage Junction Temperature Range	-55 to +150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


THERMAL CHARACTERISTICS

Symbol	Parameter	Value	Unit
$R_{\theta JC}$	Thermal Resistance, Junction to Case	3	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient (Note 1a)	60	

V_{DS}	$R_{DS(ON)} \text{ MAX}$	$I_D \text{ MAX}$
200 V	200 mΩ @ 10 V	9.5 A
	215 mΩ @ 6 V	



N-CHANNEL MOSFET




Top

Bottom

WDFN8 3.3 x 3.3, 0.65P
CASE 511DH

MARKING DIAGRAM



FDMC2610 = Specific Device Code

A = Assembly Site

L = Wafer Lot Number

YW = Assembly Start Week

ORDERING INFORMATION

Device	Package	Shipping [†]
FDMC2610	WDFN8 (Pb-Free, Halide Free)	3000 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, [BRD8011/D](#).

FDMC2610

ELECTRICAL CHARACTERISTICS ($T_J = 25^\circ\text{C}$ unless otherwise noted)

Symbol	Parameter	Test Condition	Min	Typ	Max	Unit
--------	-----------	----------------	-----	-----	-----	------

OFF CHARACTERISTICS

BV_{DSS}	Drain to Source Breakdown Voltage	$I_D = 250 \mu\text{A}, V_{\text{GS}} = 0 \text{ V}$	200	–	–	V
$\Delta \text{BV}_{\text{DSS}} / \Delta T_J$	Breakdown Voltage Temperature Coefficient	$I_D = 250 \mu\text{A}$, referenced to 25°C	–	199	–	$\text{mV}/^\circ\text{C}$
I_{DSS}	Zero Gate Voltage Drain Current	$V_{\text{DS}} = 160 \text{ V}, V_{\text{GS}} = 0 \text{ V}$	–	–	1	μA
		$V_{\text{DS}} = 160 \text{ V}, V_{\text{GS}} = 0 \text{ V}, T_J = 125^\circ\text{C}$	–	–	100	
I_{GSS}	Gate to Source Leakage Current	$V_{\text{GS}} = \pm 20 \text{ V}, V_{\text{DS}} = 0 \text{ V}$	–	–	± 100	nA

ON CHARACTERISTICS

$V_{\text{GS}(\text{th})}$	Gate to Source Threshold Voltage	$V_{\text{GS}} = V_{\text{DS}}, I_D = 250 \mu\text{A}$	2	3.2	4	V
$\Delta V_{\text{GS}(\text{th})} / \Delta T_J$	Gate to Source Threshold Voltage Temperature Coefficient	$I_D = 250 \mu\text{A}$, referenced to 25°C	–	–9.9	–	$\text{mV}/^\circ\text{C}$
$R_{\text{DS}(\text{on})}$	Drain to Source On Resistance	$V_{\text{GS}} = 10 \text{ V}, I_D = 2.2 \text{ A}$	–	175	200	$\text{m}\Omega$
		$V_{\text{GS}} = 6 \text{ V}, I_D = 1.5 \text{ A}$	–	188	215	
		$V_{\text{GS}} = 10 \text{ V}, I_D = 2.2 \text{ A}, T_J = 125^\circ\text{C}$	–	347	397	
g_{FS}	Forward Transconductance	$V_{\text{DS}} = 5 \text{ V}, I_D = 2.2 \text{ A}$	–	7	–	S

DYNAMIC CHARACTERISTICS

C_{iss}	Input Capacitance	$V_{\text{DS}} = 100 \text{ V}, V_{\text{GS}} = 0 \text{ V}, f = 1 \text{ MHz}$	–	720	960	pF
C_{oss}	Output Capacitance		–	41	55	pF
C_{rss}	Reverse Transfer Capacitance		–	12	20	pF
R_g	Gate Resistance	$f = 1 \text{ MHz}$	–	0.7	–	Ω

SWITCHING CHARACTERISTICS

$t_{\text{d}(\text{on})}$	Turn-On Delay Time	$V_{\text{DD}} = 100 \text{ V}, I_D = 2.2 \text{ A}, V_{\text{GS}} = 10 \text{ V}, R_{\text{GEN}} = 24 \Omega$	–	17	31	ns
t_r	Rise Time		–	13	24	ns
$t_{\text{d}(\text{off})}$	Turn-Off Delay Time		–	29	47	ns
t_f	Fall Time		–	16	29	ns
$Q_{\text{g}(\text{TOT})}$	Total Gate Charge at 10 V		–	12.3	18	nC
Q_{gs}	Gate to Source Gate Charge	$V_{\text{DD}} = 100 \text{ V}, I_D = 2.2 \text{ A}$	–	3	–	nC
Q_{gd}	Gate to Drain "Miller" Charge	$V_{\text{DD}} = 100 \text{ V}, I_D = 2.2 \text{ A}$	–	3.6	–	nC

DRAIN-SOURCE DIODE CHARACTERISTICS

V_{SD}	Source to Drain Diode Forward Voltage	$V_{\text{GS}} = 0 \text{ V}, I_S = 2.2 \text{ A}$ (Note 2)	–	0.8	1.2	V
t_{rr}	Reverse Recovery Time	$I_F = 2.2 \text{ A}, di/dt = 100 \text{ A}/\mu\text{s}$	–	69	104	ns
Q_{rr}	Reverse Recovery Charge		–	114	171	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

NOTES:

1. $R_{\theta JA}$ is determined with the device mounted on a 1 in² oz copper pad on a 1.5 × 1.5 in. board of FR-4 material. $R_{\theta JC}$ is guaranteed by design while $R_{\theta CA}$ is determined by the user's board design.



a) 60°C/W when mounted on a 1 in² pad of 2 oz copper.



b) 135°C/W when mounted on a minimum pad of 2 oz copper.

2. Pulse Test: Pulse Width < 300 μs , Duty cycle < 2.0%.
3. Starting $T_J = 25^\circ\text{C}$; N-ch: $L = 3 \text{ mH}, I_{AS} = 2 \text{ A}, V_{DD} = 200 \text{ V}, V_{GS} = 10 \text{ V}$.

TYPICAL CHARACTERISTICS


(T_J = 25°C unless otherwise noted)

Figure 1. On-Region Characteristics




Figure 2. Normalized On-Resistance vs. Drain Current and Gate Voltage




Figure 3. Normalized On-Resistance vs. Junction Temperature




Figure 4. On-Resistance vs. Gate to Source Voltage




Figure 5. Transfer Characteristics











Figure 6. Source to Drain Diode Forward Voltage vs. Source Current

TYPICAL CHARACTERISTICS (continued)

($T_J = 25^\circ\text{C}$ unless otherwise noted)



TYPICAL CHARACTERISTICS (continued) $(T_J = 25^\circ\text{C} \text{ unless otherwise noted})$ **Figure 13. Transient Thermal Response Curve**



POWERTRENCH is a registered trademark of Semiconductor Components Industries, LLC dba “**onsemi**” or its affiliates and/or subsidiaries in the United States and/or other countries.

WDFN8 3.3x3.3, 0.65P



CASE 511DH

ISSUE 0

DATE 31 JUL 2016



RECOMMENDED LAND PATTERN



BOTTOM VIEW

NOTES:

- A. DOES NOT CONFORM TO JEDEC
REGISTRATION MO-229
- B. DIMENSIONS ARE IN MILLIMETERS.
- C. DIMENSIONS AND TOLERANCES PER
ASME Y14.5M, 2009.
- D. LAND PATTERN RECOMMENDATION IS
EXISTING INDUSTRY LAND PATTERN

DOCUMENT NUMBER:	98AON13625G	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	WDFN8 3.3X3.3, 0.65P	PAGE 1 OF 1

onsemi and **ONSEMI** are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

onsemi, **ONSEMI**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales

