
Part Number : 1200868850
Product Description : M8 Signal, B-Coded, Single-Ended Cordset, 5 Poles, Male (90°), 0.25mm² (24 AWG), Black PUR LS0H Cable, 1.0m (3.28') Length
Series Number : 120086
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : 405007H08M010



Documents and Resources

Drawings

1200868850_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	120086
Description	M8 Signal, B-Coded, Single-Ended Cordset, 5 Poles, Male (90°), 0.25mm^2 (24 AWG), Black PUR LS0H Cable, 1.0m (3.28') Length
IP Rating	IP67
Product Name	M8 Signal,Nano-Change (M8)
Type	Single Ended
UPC	191128974592

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	30V AC/DC

Physical

Cable Diameter	4.70mm (.185")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Black
Connector End A	M8 Signal
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	B-Coded
LED Indicator	None
Material - Cable Jacket	PUR
Material - Connector Body	TPU
Material - Contact	Brass

Downloaded from Arrow.com.

Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	125.000/g
Orientation	90° to Pigtail
Poles	5
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	UL 21198
Wire Size (AWG)	24

Downloaded from Arrow.com.