


P/N 3386-18-1-0500-0XX-1-TS



UL3386 XLPE Wire 105°C 600V (18AWG)

CONSTRUCTION:	Tinned Strands, copper conductor, 34/0.180mm strands. Overall Diameter=2.80+/-0.10mm Insulation Thickness: 0.76mm
CERTIFICATION & APPROVALS:	DUAL-RATED AWM: Can be used in USA and Canada UL Subject 758 UL FILE NO:E108485 CSA Standard CSA FILE NO:LL84687 Printed Markings: AWG 3386 105°C 600V E108485-S ()AWG -H- REI HSING CSA AWM I A 125° 300V LL84687 ()AWG FT2 HF
PHYSICAL & ELECTRICAL PROPERTIES:	Rated Temperature: 105°C ~ -10°C Rated Voltage: 600V Insulation Potential Strength: 2000 VAC/min. Flexibility: XLPE Insulation Maximum Conductor Resistance: 24.4 ohm/km Resistant to: Oil, hot & cold, lighter, flexing.
APPLICATIONS:	XLPE Wire, pass FT2 flame test Halogen Free (Cl, Br <=900ppm each, CL+BL <=1500 ppm in total) Suitable for internal wires of household appliance, headlamp, mechanical etc.
PACKAGING:	500ft per reel.
ENVIRONMENTAL APPROVALS:	Conforms to all current RoHS directives as laid out in EU Directive 2011/65/EC. Current SGS reports for this wire are available upon request.

P/N's & COLORS

3386-18-1-0500-001-1-TS BLACK	3386-18-1-0500-002-1-TS WHITE	3386-18-1-0500-003-1-TS YELLOW	3386-18-1-0500-004-1-TS RED	3386-18-1-0500-005-1-TS BLUE
3386-18-1-0500-006-1-TS BROWN	3386-18-1-0500-007-1-TS GREEN	3386-18-1-0500-008-1-TS ORANGE	3386-18-1-0500-010-1-TS VIOLET	3386-18-1-0500-011-1-TS GREEN + YELLOW