




Part Number : [1041148017](#)
Product Description : 0.50mm Pitch Easy-On FFC/
FPC Slim Connector, Surface Mount, Right-Angle,ZIF,
Bottom Contact Style, Front Flip, 1.50mm Mated
Height, Gold (Au) Plating, 80 Circuits
Series Number : 104114
Status : Obsolete
Product Category : FFC / FPC Connectors




Documents & Resources

Specifications

[1041148017-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	FFC / FPC Connectors
Series	104114
Description	0.50mm Pitch Easy-On FFC/FPC Slim Connector, Surface Mount, Right-Angle,ZIF, Bottom Contact Style, Front Flip, 1.50mm Mated Height, Gold (Au) Plating, 80 Circuits
Comments	Black Actuator
Product Name	Easy-On
UPC	884982410640

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V

Physical

Actuator Type	Front Flip
Circuits (Loaded)	80
Color - Resin	Natural
Contact Position	Bottom
Durability (mating cycles max)	20
Mated Height	1.50mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	0.459/g
Orientation	Right Angle

Packaging Type	Embossed Tape on Reel
PCB Mounting	Surface Mount
PCB Retention	Yes
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.102µm
Plating min - Termination	0.051µm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-20° to +85°C
Wire/Cable Type	FFC/FPC

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	REFLOW
Max-Cycle	1
Max-Temp	250

This document was generated on Sep 11, 2025