Part Number : 1201080357
Product Description : Micro-Change (M12) to Standard RJ-45 Double-Ended Cordset, 4 Poles, D-Coded, Male (Straight) to Male (Straight), 24 AWG, TPE Cable, 25.0m (82.02') Length, 6.35mm (.250") Diameter, Orange
Series Number : 120108
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : E16A06008M250



Documents and Resources

Drawings

1201080357_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	120108
Description	Micro-Change (M12) to Standard RJ-45 Double-Ended Cordset, 4 Poles, D-Coded, Male (Straight) to Male (Straight), 24 AWG, TPE Cable, 25.0m (82.02') Length, 6.35mm (.250") Diameter, Orange
IP Rating	IP67 (M12 only)
Performance Category	5e
Product Name	Industrial Ethernet,Micro-Change (M12)
Protocol	EtherNet
Type	Double Ended
UPC	78172542929

Agency

UL	E361772

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	30V

Physical

Cable Diameter	6.35mm (.250")
Cable Length	25.0m (82.02')
Color - Cable Jacket	Orange
Connector End A	Micro-Change (M12)
Connector End B	RJ-45 (standard)

Downloaded from Arrow.com.

Coupling Style	Threaded
Gender	Male-Male
Keyway	D-Coded
LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	PUR, PVC
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	TPE
Wire Size (AWG)	24

Downloaded from Arrow.com.