
MOSFET

OptiMOS™ 5 Power-MOSFET, 25 V

TSDSON-8 FL
(enlarged source interconnection)



Features

- Optimized for high performance buck converters
- Monolithic integrated Schottky-like diode
- Very low on-resistance $R_{DS(on)}$ @ V_{GS}=4.5 V
- 100% avalanche tested
- N-channel
- Qualified according to JEDEC[1)] for target applications
- Pb-free lead plating; RoHS compliant
- Halogen-free according to IEC61249-2-21




Table 1 Key Performance Parameters

Parameter	Value	Unit
V_{DS}	25	V
$R_{DS(on),max}$	1.7	mΩ
I_D	134	A
Q_{OSS}	17.5	nC
Q_G(0V..4.5V)	10.5	nC

Type / Ordering Code	Package	Marking	Related Links
BSZ017NE2LS5I	PG-TSDSON-8 FL	17NE25I	-

[1)] J-STD20 and JESD22

Downloaded from Arrow.com.

Table of Contents

Description 1
Maximum ratings 3
Thermal characteristics 3
Electrical characteristics 4
Electrical characteristics diagrams 6
Package Outlines 10
Revision History 11
Trademarks 11
Disclaimer 11

Downloaded from Arrow.com.

1 Maximum ratings

at T_A=25 °C, unless otherwise specified

Table 2 Maximum ratings

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Continuous drain current[1]	I_D	- - - - -	- - - - -	134 85 115 73 27	A	V_{GS}=10 V, T_C=25 °C V_{GS}=10 V, T_C=100 °C V_{GS}=4.5 V, T_C=25 °C V_{GS}=4.5 V, T_C=100 °C V_{GS}=10 V, T_A=25 °C, R_{thJA}=60 K/W[2]
Pulsed drain current[3]	$I_{D,pulse}$	-	-	536	A	T_C=25 °C
Avalanche current, single pulse[4]	I_{AS}	-	-	20	A	T_C=25 °C
Avalanche energy, single pulse	E_{AS}	-	-	40	mJ	I_D=20 A, R_{GS}=25 Ω
Gate source voltage	V_{GS}	-16	-	16	V	-
Power dissipation	P_{tot}	- -	- -	50 2.1	W	T_C=25 °C T_A=25 °C, R_{thJA}=60 K/W[2]
Operating and storage temperature	T_j, T_{stg}	-55	-	150	°C	IEC climatic category; DIN IEC 68-1: 55/150/56

2 Thermal characteristics

Table 3 Thermal characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Thermal resistance, junction - case	R_{thJC}	-	-	2.5	K/W	-
Device on PCB, 6 cm² cooling area[2]	R_{thJA}	-	-	60	K/W	-

[1] Rating refers to the product only with datasheet specified absolute maximum values, maintaining case temperature at 25°C. For higher case temperature please refer to Diagram 2. De-rating will be required based on the actual environmental conditions.
[2] Device on 40 mm x 40 mm x 1.5 mm epoxy PCB FR4 with 6 cm² (one layer, 70 µm thick) copper area for drain connection. PCB is vertical in still air.
[3] See Diagram 3 for more detailed information
[4] See Diagram 13 for more detailed information

Downloaded from Arrow.com.

3 Electrical characteristics

at T_j=25 °C, unless otherwise specified

Table 4 Static characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Drain-source breakdown voltage	$V_{(BR)DSS}$	25	-	-	V	V_{GS}=0 V, I_D=10 mA
Breakdown voltage temperature coefficient	$dV_{(BR)DSS}/dT_j$	-	15	-	mV/K	I_D=10 mA, referenced to 25 °C
Gate threshold voltage	$V_{GS(th)}$	1.2	-	2	V	V_{DS}=V_{GS}, I_D=250 µA
Zero gate voltage drain current	I_{DSS}	- -	- 0.5	0.5 -	mA	V_{DS}=20 V, V_{GS}=0 V, T_j=25 °C V_{DS}=20 V, V_{GS}=0 V, T_j=125 °C
Gate-source leakage current	I_{GSS}	-	10	100	nA	V_{GS}=20 V, V_{DS}=0 V
Drain-source on-state resistance	$R_{DS(on)}$	- -	1.9 1.45	2.3 1.7	mΩ	V_{GS}=4.5 V, I_D=20 A V_{GS}=10 V, I_D=20 A
Gate resistance	R_G	-	0.85	1.4	Ω	-
Transconductance	g_{fs}	60	120	-	S	$\|V_{DS}\|>2\|I_D\|R_{DS(on)max}$, I_D=20 A

Table 5 Dynamic characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Input capacitance[1)]	C_{iss}	-	1500	2000	pF	V_{GS}=0 V, V_{DS}=12 V, f=1 MHz
Output capacitance[1)]	C_{oss}	-	750	1000	pF	V_{GS}=0 V, V_{DS}=12 V, f=1 MHz
Reverse transfer capacitance	C_{rss}	-	60	-	pF	V_{GS}=0 V, V_{DS}=12 V, f=1 MHz
Turn-on delay time	$t_{d(on)}$	-	4	-	ns	V_{DD}=12 V, V_{GS}=10 V, I_D=30 A, $R_{G,ext}$=1.6 Ω
Rise time	t_r	-	4	-	ns	V_{DD}=12 V, V_{GS}=10 V, I_D=30 A, $R_{G,ext}$=1.6 Ω
Turn-off delay time	$t_{d(off)}$	-	20	-	ns	V_{DD}=12 V, V_{GS}=10 V, I_D=30 A, $R_{G,ext}$=1.6 Ω
Fall time	t_f	-	3	-	ns	V_{DD}=12 V, V_{GS}=10 V, I_D=30 A, $R_{G,ext}$=1.6 Ω

[1)] Defined by design. Not subject to production test.

Downloaded from Arrow.com.

Table 6 Gate charge characteristics[1)]

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Gate to source charge	Q_{gs}	-	3.7	-	nC	V_{DD}=12 V, I_D=30 A, V_{GS}=0 to 4.5 V
Gate charge at threshold	$Q_{g(th)}$	-	2.4	-	nC	V_{DD}=12 V, I_D=30 A, V_{GS}=0 to 4.5 V
Gate to drain charge	Q_{gd}	-	2.3	-	nC	V_{DD}=12 V, I_D=30 A, V_{GS}=0 to 4.5 V
Switching charge	Q_{sw}	-	3.5	-	nC	V_{DD}=12 V, I_D=30 A, V_{GS}=0 to 4.5 V
Gate charge total	Q_g	-	10.5	14	nC	V_{DD}=12 V, I_D=30 A, V_{GS}=0 to 4.5 V
Gate plateau voltage	$V_{plateau}$	-	2.4	-	V	V_{DD}=12 V, I_D=30 A, V_{GS}=0 to 4.5 V
Gate charge total[2)]	Q_g	-	22	30	nC	V_{DD}=12 V, I_D=30 A, V_{GS}=0 to 10 V
Gate charge total, sync. FET	$Q_{g(sync)}$	-	9.8	-	nC	V_{DS}=0.1 V, V_{GS}=0 to 4.5 V
Output charge[2)]	Q_{oss}	-	17.5	24	nC	V_{DD}=12 V, V_{GS}=0 V

Table 7 Reverse diode


Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Diode continuous forward current	I_S	-	-	50	A	T_C=25 °C
Diode pulse current	$I_{S,pulse}$	-	-	536	A	T_C=25 °C
Diode forward voltage	V_{SD}	-	0.51	0.65	V	V_{GS}=0 V, I_F=7 A, T_j=25 °C
Reverse recovery charge	Q_{rr}	-	12	-	nC	V_R=12 V, I_F=I_S, di_F/dt=400 A/µs

[1)] See "Gate charge waveforms" for parameter definition
[2)] Defined by design. Not subject to production test.

Downloaded from Arrow.com.


4 Electrical characteristics diagrams

Diagram 1: Power dissipation




$P_{tot}=f(T_C)$

Diagram 2: Drain current




$I_D=f(T_C)$; $V_{GS}\geq 10$ V

Diagram 3: Safe operating area



$I_D=f(V_{DS})$; T_C=25 °C; D=0; parameter: t_p


Diagram 4: Max. transient thermal impedance



$Z_{thJC}=f(t_p)$; parameter: $D=t_p/T$


Downloaded from Arrow.com.

Diagram 5: Typ. output characteristics




$I_D=f(V_{DS})$; $T_j=25$ °C; parameter: V_{GS}

Diagram 6: Typ. drain-source on resistance




$R_{DS(on)}=f(I_D)$; $T_j=25$ °C; parameter: V_{GS}

Diagram 7: Typ. transfer characteristics



$I_D=f(V_{GS})$; $|V_{DS}|>2|I_D|R_{DS(on)max}$; parameter: T_j


Diagram 8: Typ. forward transconductance



$g_{fs}=f(I_D)$; $T_j=25$ °C


Downloaded from Arrow.com.

Diagram 9: Drain-source on-state resistance




$R_{DS(on)}$=f(T_j); I_D=20 A; V_{GS}=10 V

Diagram 10: Typ. gate threshold voltage




$V_{GS(th)}$=f(T_j); V_{GS}=V_{DS}

Diagram 11: Typ. capacitances



C=f(V_{DS}); V_{GS}=0 V; f=1 MHz


Diagram 12: Forward characteristics of reverse diode



I_F=f(V_{SD}); parameter: T_j


Downloaded from Arrow.com.

Diagram 13: Avalanche characteristics




I_{AS}=f(t_{AV}); R_{GS}=25 Ω; parameter: $T_{j(start)}$

Diagram 14: Typ. gate charge




V_{GS}=f(Q_{gate}); I_D=30 A pulsed; parameter: V_{DD}

Diagram 15: Typ. drain-source leakage current



I_{DSS}=f(V_{DS}); V_{GS}=0 V; parameter: T_j


Diagram Gate charge waveforms



Downloaded from Arrow.com.

5 Package Outlines

TSDSON-8-25/-26



DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	0.90	1.10	0.035	0.043
b	0.24	0.44	0.009	0.017
b1	0.10	0.30	0.004	0.012
b2	0.24	0.44	0.009	0.017
D=D1	3.20	3.40	0.126	0.134
D2	2.19	2.39	0.086	0.094
D3	1.54	1.74	0.061	0.069
D4	0.21	0.41	0.008	0.016
E	3.20	3.40	0.126	0.134
E4	2.01	2.21	0.079	0.087
E6	0.10	0.30	0.004	0.012
e	0.65 (BSC)		0.026 (BSC)	
N	8		8	
L	0.30	0.51	0.012	0.020
L1	0.40	0.70	0.016	0.028
L2	0.50	0.70	0.020	0.028
aaa	0.25		0.010	
F1	3.90		0.154	
F2	2.29		0.090	
F3	0.31		0.012	
F4	0.34		0.013	
F5	0.80		0.031	
F6	1.00		0.039	
F7	2.51		0.099	
F8	1.64		0.065	
F9	0.50		0.020	

DOCUMENT NO.
Z8B00158553

SCALE
0 2.5 5mm

EUROPEAN PROJECTION

ISSUE DATE
27-12-2010

REVISION
02

Figure 1 Outline PG-TSDSON-8 FL, dimensions in mm/inches

Downloaded from Arrow.com.

Revision History

BSZ017NE2LS5I

Revision: 2020-06-17, Rev. 2.1

Previous Revision		
Revision	Date	Subjects (major changes since last revision)
2.0	2015-08-17	Release of final version
2.1	2020-06-17	Update current rating

Trademarks
All referenced product or service names and trademarks are the property of their respective owners.

We Listen to Your Comments
Any information within this document that you feel is wrong, unclear or missing at all? Your feedback will help us to continuously improve the quality of this document. Please send your proposal (including a reference to this document) to:
erratum@infineon.com

Published by
Infineon Technologies AG
81726 München, Germany
© 2020 Infineon Technologies AG
All Rights Reserved.

Legal Disclaimer
The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics (“Beschaffenheitsgarantie”) .

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.
In addition, any information given in this document is subject to customer’s compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer’s products and any use of the product of Infineon Technologies in customer’s applications.
The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer’s technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Information
For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office (www.infineon.com).

Warnings
Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.
The Infineon Technologies component described in this Data Sheet may be used in life-support devices or systems and/or automotive, aviation and aerospace applications or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support, automotive, aviation and aerospace device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

Downloaded from Arrow.com.