



Part Number : [1200658194](#)
Product Description : Micro-Change (M12)
Single-Ended Cordset, 4 Poles, Female (90°) to
Pigtail, 0.34mm² Black PUR LSOH Cable,
10.0m (32.81') Length
Series Number : 120065
Status : Active
Product Category : Circular Industrial
Cordsets
Engineering Number : 804001H09M100



Documents & Resources

Drawings
[1200658194_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead... per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120065
Description	Micro-Change (M12) Single-Ended Cordset, 4 Poles, Female (90°) to Pigtail, 0.34mm ² Black PUR LSOH Cable, 10.0m (32.81') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Protocol	N/A
Type	Single Ended
UPC	883906397746

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V

Physical

Cable Diameter	4.70mm (.185")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	None

Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	318.465/g
Orientation	90° to Pigtail
Poles	4
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	UL 21198
Wire Size (AWG)	22

This document was generated on Apr 26, 2025