

HUBER+SUHNER® DATA SHEET

Coaxial PCB Connector: 85_1023-C50-0-1/111_N

Rev.: D



Description

Right angle PCB jack

Interface Standards
DIN 41626/2



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 4 GHz

Mechanical Data

Board mounting type through holes
Weight 0.0025 kg

Environmental Data

Operating Temperature -55 °C to 125 °C
2002/95/EC (RoHS) compliant

Material Data

Piece Parts

Centre contact	Copper Beryllium Alloy
Outer contact	Brass
Body	Brass
Insulator	PFA / PTFE

Surface Plating

Hard Au min. 1.3 μm over Ni min. 1.3 μm
Gold Plating (Nickel underplated)
Hard Au min. 0.8 μm over Ni min. 1.3 μm

Related Documents

Outline drawing	DOU-00013127
Catalogue drawing	DCA-00013129

Ordering Information

Single package	85_1023-C50-0-1/111_NE
----------------	------------------------

Remarks

PCB connector with stand-offs

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER

HUBER+SUHNER AG

RF Technology

9100 Herisau, Switzerland

Phone +41 (0)71 353 41 11

Fax +41 (0)71 353 45 90

www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions

Document: DOC-0000193419 G

Issued: 11.03.11

Uncontrolled Copy

Page 1/1