











PRODUCT NO.
61729-*



TYPE"4" PARTIAL BACK
WITH SHORT SOLDER TAIL,
SHELL TAIL AND SPECIAL
HOUSING FOR PIP PROCESS
61729-XXWXL

TYPE"5" PARTIAL BACK WITH SHORT
SOLDER TAIL, SHORT SHELL TAIL AND
SELECTED MATTE TIN SHELL FOR
PIP PROCESS 61729-XXTXLF

TYPE"6" PARTIAL BACK WITH SHORT
SOLDER TAIL, SHORT SHELL TAIL,
SPECIAL HOUSING, AND FULL MATTE
TIN SHELL FOR PIP PROCESS
61729-XXVXL



TYPE"1" FULL BACK


TYPE"2" PARTIAL BACK

TYPE"3" PARTIAL BACK WITH SHORT
SOLDER TAIL AND SHELL TAIL FOR
PIP PROCESS 61729-XXQLF


mat'l. code				surface	tolerance	projection	product family
				ISO 1302 ✓	ISO 406 ISO 1101	1101	HPL 511 USB2.0
ltr	ecn	no	dr	date	tolerances unless otherwise specified	mm	title
AA	ELX-N-34768-1	YY	09/19/19	angles	0.0±0.30		USB RECEPTACLE B TYPE
AB	ELX-N-37746-1	YY	03/09/21	linear	0.00±0.20		
AC	ELX-N-40307-1	YY	03/09/21	0°±2°	0.000±0.10	scale 1:1	
AD	ELX-N-45469-1	TY	07/22/22	dr	Yuan-Yuan Bao 07/22/22		
				engr	Tian-Yu.Tang 07/22/22		
X	ELX-N-29556	LZ	03/09/18	chr	Li-Qing Lei 07/22/22		
Y	ELX-N-32780	YY	02/26/19	appd	Tim.Yao 07/22/22		
sheet	revision						
index	sheet						

dwg no sheet 1 of 3 size
61729 A3

type Product Customer Drawing



P.C. BOARD LAYOUT
STYLE 1 APPLY FOR TYPE 1 & 2




P.C. BOARD LAYOUT
STYLE 2 APPLY FOR TYPE 3

NOTES:

1. MATERIAL:
SHIELD & CONTACTS: COPPER ALLOY
HOUSING: UL 94V-0 ,HIGH TEMPERATURE THERMOPLASTIC.
COLOR: SEE PRODUCT NUMBER CODE.
2. PLATING: SEE PRODUCT NUMBER CODE.
SHIELD: BRIGHT TIN, NICKEL UNDERPLATE(USED FOR WAVE SOLDER PROCESS),
PLATING NICKEL ONLY(USED FOR PIP PROCESS).
3. DATUMS & BASIC DIMENSIONS TO BE DETERMINED BY CUSTOMER
4. RECOMMENDED BOARD THICKNESS IS 1.57 mm (.062)
5. PACKING STANDARD GS-14-920 WILL BE APPLIED FOR LEAD FREE P/N'S
6. FOR LEAD FREE P/N, THE PRODUCT MEET EUROPEAN UNION DIRECTIVES AND
OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008
7. FOR LEAD FREE P/N'S, THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C
PEAK TERMERATURE FOR 10 SECONDS IN A CONVECTION, INFRO-RED OR VAPOR
PHASE REFLOW OVEN.
8. THE PART CAN BE USED FOR PIP PROCESS.

mat'l. code				surface	tolerance	projection	product family		
				ISO 1302 ✓	ISO 406 ISO 1101	1101	HPL 511 USB2.0		
ltr	ecn no	dr	date	tolerances unless otherwise specified			title		
AD				angles	linear	mm	USB RECEPTACLE B TYPE		
				0°±2°	0.0±0.30				
					0.00±0.20				
					0.000±0.10	scale 1:1			
				dr	Yuan-Yuan Bao	07/22/22	dwg no		
				engr	Tian-Yu.Tang	07/22/22	sheet2 of 3		
				chr	Li-Qing Lei	07/22/22	61729		
				appd	Tim Yao	07/22/22	A3		
sheet index				revision sheet			type Product Customer Drawing		

PRODUCT NUMBER CODE:



mat'l. code				surface		tolerance		projection		product family				
				ISO 1302 ✓		ISO 406 ISO 1101				HPL 511 USB2.0				
ltr	ecn	no	dr	date		tolerances unless otherwise		specified		title				
AD						angles		0.0±0.30		USB RECEPTACLE B TYPE				
						linear		0.00±0.20						
						0°±2°		0.000±0.10						
								scale 1:1						
				dr	Yuan-Yuan Bao		07/22/22				dwg no		sheet3 of 3	size
				engr	Tian-Yu.Tang		07/22/22				61729		A3	
				chr	Li-Qing Lei		07/22/22							
				appd	Tim.Yao		07/22/22							
sheet index		revision sheet								type		Product	Customer	Drawing