

HANDHELD COMPUTERS

CN51 Handheld Computer

CN51 Handheld-Computer

Overview

Specifications

Resources

SKUs



Save this page as PDF

SUPPORT

WHERE TO BUY

CONTACT US

The Honeywell CN51 device offers you unparalleled versatility with your choice of Windows® or Android™ operating systems. Add to that a power-packed 1.5 GHz dual core, multiengine processor, 1 GB RAM and 16 GB Flash and you have the highest degree of future-proofing capability too. A 5-megapixel color camera adds to the device's capabilities.

- Supports Microsoft® Windows Embedded Handheld 6.5 and Android 6.0 Marshmallow operating systems for flexible application support and migration.
- Features best-in-class motion tolerance and support for omnidirectional 1D and 2D barcode scanning.
- Features WAN radio options with voice and data support including UMTS and Flexible Network UMTS/ CDMA, PTT, as well as 802.11 a/b/g/n, Bluetooth® and GPS with GLONASS support.
- Withstands multiple 1.5-meter (5-feet) drops to concrete across the operating temperature range and has an IP64 seal rating against rain and dust.
- Large 4-inch brilliant WVGA multi-touch display allows for more graphical user interface, display-centric applications.

Designed for a superior user experience. The CN51 mobile computer's large, multi-touch, outdoor-readable screen provides ample room for application viewing. Less scrolling. Greater productivity. And more space for capturing signatures too. Inside the CN51 computer, state-of-the-art smart battery technology delivers enough power to last a full shift. It also cuts the cost for replacement batteries.

Additional features and benefits include:

- High-performance imager provides quick, accurate barcode scanning even in low light.
- Unmatched motion tolerance eliminates costly delays and user frustration during scan-intensive applications.
- 5-megapixel color camera and our cutting-edge image processing technologies deliver advanced capability beyond reading barcodes.
- Mobile Document Imaging (MDI) and Remote Deposit Capture (RDC) provide a fast and reliable way to convert full-size paper documents or check payments into electronic files. Transmit files directly from the point of capture to the back-office workflow.
- CloneNGo device provisioning makes it easy to replicate a master configuration across an unlimited number of devices to get up and running quickly.
- Honeywell SmartSystems™ Foundation monitors key subsystems to prevent issues before they impact operations.



Let's Connect!

Sign up to receive exclusive communications from Honeywell including product updates, technical information, new offerings, events and news, surveys, special offers, and related topics via telephone, email, and other forms of electronic communication.

SUBSCRIBE

PRODUCTS

Advanced Sensing Technologies

Automation

Productivity

Safety

More Products

SOFTWARE

Automation

Productivity

Safety

SERVICES

Automation

Productivity

Safety

INDUSTRIES

Healthcare & Life Sciences

Transportation & Logistics

Manufacturing

Distribution Centers

Retail

E-Commerce

Government

Aerospace & Defense

WHERE TO BUY

Advanced Sensing Technologies

Automation

Productivity

Safety

COMPANY

About Honeywell

About SPS

News

Press Releases

Investors

Events

CAREERS

Careers

Job Search

CONTACT

Contact Us

Support

Unsubscribe

Notifications

FOLLOW US

