


ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	COMPONENT NOTES
1	50-00903	Connector, 4C audio jack, 3.5x7.0xL19.5 mm, brass, nickel plated, molding style	1	
2	30-00180	Wire, 3C BC, 28 AWG, 300V, 80C, 3.8 mm, foil + shield, PVC, white	1	
3	24-00267	Overmold, audio jack, 3.5 mm, twist lock panel mount, TIC	1	PVC, white
4	56-00000	Hardware, nut, hex, 13x2.5 mm, M11x1.0, brass, nickel plated	1	
5	56-00001	Hardware, washer, lock, 14x11.1x1.1 mm, SPCC, nickel plated	1	
6	Heat Shrink	Heat shrink tubing, white	1	
7	Heat shrink	Heat shrink tubing, black	1	Covers shield wire



Revision:	Date:	Description:	Prepared:	Notes:	TENSILITY tel 1.541.323.3228 800 877.670.7118 fax 1.541.323.4202 web tensility.com Size: A Scale: 1:1 Part number: 10-03410 Sheet 1 of 1
A	9/24/2019	Initial release	CR	RoHS compliant	
			Verified: KW	Function test: no open, no short circuit, no intermittent	
			Dimensions are in millimeters.	Description:	
			Tolerances:	Cable, 305 mm, 3.5 mm 4C 50-00903 twist lock panel mount audio jack to 5 mm tinned, 28 AWG, white	