

Product data sheet

Miniature connectors




Product description	M16 Female angled connector, Contacts: 24, 6.0-8.0 mm, shieldable, solder, IP67, UL 2238
Area	M16 IP67
Series	423
Part no.	99 5696 75 24


Illustration (may vary)



Scale drawing



Contact arrangement (Plug-in side)



You can find the assembly instructions on the next page.

Technical data

General features

Part no.	99 5696 75 24
Connector design	Female angled connector
Version	Connector socket angled
Connector locking system	screw
Termination	solder
Degree of protection	IP67
Connection cross-section	0.14 mm² / AWG 26
Cable outlet	6.0-8.0 mm
Twistability	90° (4 coding options)
Temperature range from/to	-30 °C / 95 °C
Mechanical operation	> 500 Mating cycles
Weight (g)	66.58
Customs tariff number	85369010
Country of Origin	DE

Electrical parameters

Rated voltage	60 V
Rated impulse voltage	500 V
Rated current	1.0 A
Insulation resistance	≥ 10 ¹⁰ Ω
Pollution degree	1
Overvoltage category	I
Insulating material group	III

Product data sheet

Miniature connectors



Product description	M16 Female angled connector, Contacts: 24, 6.0-8.0 mm, shieldable, solder, IP67, UL 2238
Area	M16 IP67
Series	423
Part no.	99 5696 75 24

EMC compliance	shieldable
Shield connection	Shielding ring

Material

Housing material	CuZn (Brass nickel plated)
Contact body material	PBT (UL94 V-0)
Contact material	CuSn (bronze)
Contact plating	Au (gold)
REACH SVHC	CAS 7439-92-1 (Lead)
SCIP number	c4034c27-44b3-4dd2-8c5a-b2ca7740bf9d

Authorization/approvals

Approvals	UL 2238
-----------	---------

Classifications

eCl@ss 11.1	27-44-01-02
ETIM 9.0	EC002635

Declarations of conformity

Low Voltage Directive	EN 60529:1991 EN 60204-1:2018
-----------------------	---------------------------------

Trade-Compliance

Copper (9903.78.01)	0.000321 kg
---------------------	-------------


Product data sheet

Miniature connectors



Product description	M16 Female angled connector, Contacts: 24, 6.0-8.0 mm, shieldable, solder, IP67, UL 2238
Area	M16 IP67
Series	423
Part no.	99 5696 75 24

Assembly instructions



Product description	M16 Female angled connector, Contacts: 24, 6.0-8.0 mm, shieldable, solder, IP67, UL 2238
Area	M16 IP67
Series	423
Part no.	99 5696 75 24

Security notices

The connector must not be plugged or unplugged under load. Non-observance and improper use can result in personal injury.

The connectors have been developed for applications in plant engineering, control and electrical equipment construction. The user is responsible for checking whether the connectors can also be used in other areas of application.

To protect against unintentional opening of the connector, the thread between the housing and the connector head must be secured with a suitable cyanoacrylate adhesive when used in circuits with voltages dangerous to the touch. This does not apply to connectors used in SELV and PELV circuits according to IEC 61140 (EN 61140, VDE 0140-1).

Connectors which are used in circuits with voltages dangerous to the touch may only be installed and used by, or under the supervision of, persons with electrical engineering training, taking into account the applicable regulations and standards.

The user must take suitable safety precautions to ensure that the connector cannot be accidentally disconnected.

Plug connectors with enclosure protection IP67 and IP68 are not suitable for use under water. When used outdoors, the plug connectors must be protected separately against corrosion. For further information on the IP protection classes, please refer to the "Technical Information" download centre.

Please observe the pollution degree and the overvoltage category. For further information, please refer to the download center "Technical Information".

To lock the cable connector with the device connector, the threaded ring is tightened "hand-tight" (approx. 60 cNm).