Part Number : 638193800
Product Description : Hand Crimp Tool for CTX64 Receptacle Terminal, 0.50, 0.75, 0.85mm² and 20 AWG
Series Number : 207129
Status : Active
Product Category : Crimp Presses and Crimp Hand Tools



## Documents & Resources

### Tooling Specifications

ATS-6381938HM-001.pdf
TM-638000029-001.pdf
TM-638000029DE-001.pdf
TM-638000029SP-001.pdf
TM-638000029FR-001.pdf
TM-638000029IT-001.pdf
TM-638000029JP-001.pdf
TM-638000029KR-001.pdf
TM-638000029MY-001.pdf
TM-638000029PL-001.pdf
TM-638000029RU-001.pdf
TM-638000029SK-001.pdf
TM-638000029TH-001.pdf
TM-638000029VN-001.pdf
TM-638000029CN-001.pdf
TM-638000029TW-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Relevant |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Relevant |
| REACH SVHC | Not Contained per ED/61/2018 (27 June 2018) |
| EU RoHS | Compliant per EU 2015/863 |

Downloaded from Arrow.com.

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Crimp Presses and Crimp Hand Tools |
| Series | 207129 |
| Description | Hand Crimp Tool for CTX64 Receptacle Terminal, 0.50, 0.75, 0.85mm$^2$ and 20 AWG |
| Comments | See Tooling Specification (PDF) Above;  Type: 4A |
| Function | Crimp |
| Geographic Area | Global |
| Level of Automation | Manual |
| More Detailed Tech Information | toolingsupport@molex.com |
| Product Name | PremiumGrade |
| Tool Type | Hand Crimp Tool |
| UPC | 883906422875 |

Downloaded from Arrow.com.

| | |
|---|---|
| Warranty Disclaimer | CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified. |

## Applicable Parts

| Description | Part Number |
|---|---|
| CTX64 Female Terminal, Tin, L-Grip, D-Wind, Left Payoff, SAE 20 | 348033212 |

This document was generated on Feb 07, 2025

Downloaded from Arrow.com.