



Part Number : 639015300

Product Description : FineAdjust Applicator for Insulation OD 1.80-2.20mm Optimized for 16 AWG Only

Series Number : 207127

Status : Obsolete

Product Category : Applicators and Crimp Modules



Documents & Resources

Tooling Specifications

[ATS-639015300-001.pdf](#)

[TM-638000029-001.pdf](#)

[TM-638000029SP-001.pdf](#)

[TM-638000029IT-001.pdf](#)

[TM-638000029JP-001.pdf](#)

[TM-638000029KR-001.pdf](#)

[TM-638000029MY-001.pdf](#)

[TM-638000029PL-001.pdf](#)

[TM-638000029RU-001.pdf](#)

[TM-638000029SK-001.pdf](#)

[TM-638000029TH-001.pdf](#)

[TM-638000029VN-001.pdf](#)

[TM-638000029CN-001.pdf](#)

[TM-638000029TW-001.pdf](#)

[TM-638004900-001.pdf](#)

[TM-638004900CN-001.pdf](#)

[TM-638004900DE-001.pdf](#)

[TM-638004900SP-001.pdf](#)

[TM-638004900FR-001.pdf](#)

[TM-638004900IT-001.pdf](#)

[TM-638004900JP-001.pdf](#)

[TM-638004900KR-001.pdf](#)

Obsolete

[TM-638004900MY-001.pdf](#)

[TM-638004900PL-001.pdf](#)

[TM-638004900RU-001.pdf](#)

[TM-638004900SK-001.pdf](#)

[TM-638004900TH-001.pdf](#)

[TM-638004900VN-001.pdf](#)

[TM-638004900TW-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Applicators and Crimp Modules

Series	207127
Description	FineAdjust Applicator for Insulation OD 1.80-2.20mm Optimized for 16 AWG Only
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	toolingsupport@molex.com
Product Name	FineAdjust
Tool Type	Applicator
UPC	884982020092
Warranty Disclaimer	<p>CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.</p>

Physical

Net Weight	4984.018/g
------------	------------

Mates With / Use With

Use with Part(s)

Description	Part Number

TM-2000 Universal Press	<u>638008300</u>
TM-2000 Universal Press (Europe 220V)	<u>638008400</u>
TM-3000 Universal Crimp Press, 120AC 50/60Hz, Used for product up to 10 AWG	<u>638017200</u>
TM-3000 Universal Crimp Press, 220AC 50/60Hz, Used for product up to 10 AWG	<u>638017300</u>
TM-4000 Universal Crimp Press, 240AC 50/60Hz, Used for product up to 4 AWG	<u>638017600</u>
Use With	Most Industry Standard Presses or Wire Process Machines

Applicable Parts

Description	Part Number
Mini-Fit Female Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass, Double 22+20, 22+18, 20+20 or Single 16 AWG, Reel	<u>39000077</u>
Mini-Fit Female Crimp Terminal, Tin (Sn) over Phosphor Bronze, Double 22+20, 22+18, 20+20 or Single 16 AWG, Reel	<u>39000079</u>
Mini-Fit Male Crimp Terminal, Tin (Sn) over Copper Plated Brass, Double 22+20, 22+18, 20+20 or Single 16 AWG, Reel	<u>39000081</u>
Mini-Fit Male Crimp Terminal, Tin (Sn) over Phosphor Bronze, Double 22+20, 22+18, 20+20 or Single 16 AWG, Reel	<u>39000083</u>
Mini-Fit Female Crimp Terminal, Gold (Au) over Brass, 16 AWG, Reel	<u>39000089</u>
Mini-Fit Male Crimp Terminal, Selective Gold (Au) and Selective Tin (Sn) over Nickel (Ni), 16 AWG, Reel	<u>39000095</u>

Mini-Fit Male Crimp Terminal, Tin (Sn) Plated Brass Contact, 16 AWG, Reel	<u>39000124</u>
Mini-Fit Male Crimp Terminal, Tin (Sn), Phosphor Bronze, 16 AWG, Reel	<u>39000130</u>
Mini-Fit Female Crimp Terminal, Selective Gold (Au) over Phosphor Bronze, 16 AWG, Reel	<u>39000185</u>
Mini-Fit Female Crimp Terminal, Tin (Sn) over Nickel (Ni), 16 AWG, Reel	<u>39000211</u>
Mini-Fit Female Crimp Terminal, Tin (Sn) over Phosphor Bronze, 16 AWG, Reel	<u>39000217</u>
Mini-Fit Male Crimp Terminal, Phosphor Bronze, Gold (Au), 16 AWG, Reel	<u>39000223</u>
Mini-Fit HCS Crimp Terminal, 16 AWG, Reel, Copper (Cu) Alloy, Tin (Sn)	<u>444763111</u>
Mini-Fit HCS Crimp Terminal, 16 AWG, Reel, Copper (Cu) Alloy, Tin (Sn)	<u>444783111</u>
Mini-Fit Plus Crimp Terminal, 16 AWG, Reel, Copper (Cu) Alloy, Tin (Sn)	<u>457503111</u>
Mini-Fit Plus Crimp Terminal, 16 AWG, Reel, Copper (Cu) Alloy, Gold (Au) Selective	<u>457503211</u>
Mini-Fit Plus Crimp Terminal, 16 AWG, Reel, Tin (Sn) Plating	<u>460123141</u>
Mini-Fit Plus Grounding Crimp Terminal, 16 AWG, Reel, Tin (Sn) Plating	<u>460123151</u>
Mini-Fit Plus Crimp Terminal, 16 AWG, Reel, 0.76µm Selective Gold (Au) Plating	<u>460123241</u>
Mini-Fit Plus Grounding Crimp Terminal, 16 AWG, Reel, 0.76µm Selective Gold (Au) Plating	<u>460123251</u>
Mini-Fit Plus High Mating Cycle	<u>460183541</u>

Female Crimp Terminal, 16 AWG, Reel, Select Gold (Au) Plating with Proprietary Molex Advanced Contact Surface Finish (CSF) in Contact Area	
Mini-Fit HCS Crimp Terminal, 16 AWG, Reel, Copper (Cu) Alloy, .76 μ m Tin (Sn)	<u>444763211</u>

This document was generated on Sep 24, 2025

Obsolete