Ratings
Voltage: 600 V
Temperature: -40~105 °C
Flammability: VW-1


Conductor
Conductor count: 1
Gauge: 28 AWG 0.09 mm²
Material: tinned copper strands
Strand size: Ø 0.127 mm x 7
Resistance at 20 °C: 250 Ω /km max

Insulator
Material: Polyphenylene Ether, Modified (mPPE)
Color: brown
Diameter: ∅0.9 ±0.08 mm
Nominal thickness: 0.25 mm
Resistance at 20 °C: 100 MΩ /km min

Wire marking: E339579 UL AWM STYLE 11028 28 AWG 105°C 600V VW-1 - - - cUL AWM I A/B 105°C 600V FT1 TENSILITY

Bend radius
Minimum: 4 times diameter (3.6 mm)





Revision:	Date:	Description:
A	3/2/2021	Initial release

Prepared: AG Digitally signed by AG Date: 2021.09.23 10:05:45 -07'00'

Verified: JD Digitally signed by JD Date: 2021.09.23 11:30:32 -07'00'

Dimensions are in millimeters.
Tolerances:
X: ± 0.5 mm
X.X: ± 0.3 mm
X.XX: ± 0.05 mm

Notes:
RoHS compliant

Phthalate and halogen free

Description:
Wire, hook-up, TS, 28 AWG, UL 11028, 600V, 105C, 0.9 mm, mPPE, brown

TENSILITY
tel 1.541.323.3228 800 877.670.7118
fax 1.541.323.4202 web tensility.com

Size: A
Part number: 30-01791
Scale: 30:1
Sheet 1 of 1

To see a custom version of this cable assembly, call Tensility at 541-323-3228 or email engineering@tensility.com

5 4 3 2 1

Downloaded from Arrow.com.