



Part Number : [2042261002](#)
Product Description : Squba 1.8 Plug Terminal,
Matte Tin Plating, 26 AWG
Series Number : 204226
Status : Active
Product Category : Crimp Terminals



Documents and Resources

Drawings

- [2042261002_sd.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

Specifications

- [2042200000-AS-000.pdf](#)
- [2042260000-PK-000.pdf](#)
- [2042200000-PS-000.pdf](#)
- [2042200000-TS-000.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	204226
Description	Squba 1.8 Plug Terminal, Matte Tin Plating, 26 AWG
Application	Wire-to-Wire
Keyword	Squba 1.8
Product Name	Squba
UPC	198282261230

Electrical

Current - Maximum per Contact	5.0A
Voltage - Maximum	125V

Physical

Durability (mating cycles max)	10
Gender	Male
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Net Weight	0.096/g
Packaging Type	Reel
Plating min - Mating	2.500µm
Plating min - Termination	2.500µm
Termination Interface Style	Crimp or Compression

Wire Insulation Diameter	0.95mm-1.40mm
Wire Size (AWG)	26
Wire Size mm ²	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
Squba 1.8 Sealed Single Row Plug Assemblies	<u>204223</u>

Application Tooling

Global

Description	Part Number
FA2 Mechanical Feed Crimp Applicator for Squba 1.80mm Plug and Receptacle Terminals, 26 AWG, UL 1007 / UL 1569 Wires	<u>2130697600</u>
Hand Crimp Tool for Squba 1.8 Plug and Receptacle Crimp Terminals, 26 AWG, UL 1569 Wire	<u>2238634700</u>

This document was generated on May 20, 2026