

DCM20-1-DC5-R-C

In Production

Recommended

RoHS

Applications

Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	Consumer equipment, Industrial Equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.

Features

Displays DC volts, amperes, watts and kilowatts.

Appearance & Shape



Attention
1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

DCM20-1-DC5-R-C



Specifications

Productseries	DMR20-0/5
Product Series Features	DMR20-0/5
Measuring Range(ACA)	0A to 1200A
Display Type	LED
Color	Red
Number of Digits	4
Digit Height (mm)	9.2mm
Power Supply Type	DC Powered
Power Supply(DCV)	9V to 72V
DC Power Supply Current (mA)Max	6mA
Operatingtemperature(degC)	0°C to 60°C
Humidity	0% to 85%
Measurment Type	DC Volts, DC Current, DC Power
Mounting Type	Panel Mount
Accuracy	+/-1%
Case Material	Polycarbonate
Configurable DPM	Yes
DC current Shunt	External
Daylight Readable	No
Digit Height (inch)	0.36inch
Resolution (V)	0.01V
Update Rate (samples /sec)	2.5
Weight (g)	29g
Weight (oz)	1.023

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.