

MHQ0603P6N2CT000

**Applications**

Commercial Grade

**Multilayer** Multilayer**Feature****Non-Mag Core** Non-Magnetic Core (Dielectric Ceramic)**Super High Q** Super High Q**Series | Type**

MHQ-P

**Status**

Production

**Brand**

TDK

**Size**

Length(L)	0.65mm $\pm$ 0.05mm
Width(W)	0.35mm $\pm$ 0.05mm
Thickness   Height	0.35mm $\pm$ 0.05mm
Recommended Land Pattern (A)	0.25mm Nom.
Recommended Land Pattern (B)	0.30mm Nom.
Recommended Land Pattern (C)	0.30mm Nom.

**Electrical Characteristics**

Inductance	6.2nH $\pm$ 0.2nH at 500MHz
Rated Current	300mA
DC Resistance [Typ.]	520m $\Omega$
DC Resistance [Max.]	700m $\Omega$
Self Resonant Frequency [Min.]	4GHz
Self Resonant Frequency [Typ.]	6.7GHz
Q [Min.]	16 at 500MHz
Q [Typ.]	

**Other**

Operating Temp. Range	-55 to 125°C
Soldering Method	Reflow
AEC-Q200	NO
Packing	Punched (Paper)Taping [180mm Reel, Tape width 8mm]
Package Quantity	15000pcs
Weight	0.0002g

! Images are for reference only and show exemplary products.





! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.

MHQ0603P6N2CT000



## Characteristic Graphs (This is reference data, and does not guarantee the products characteristics.)




! Images are for reference only and show exemplary products.  
! This PDF document was created based on the data listed on the TDK Corporation website.  
! All specifications are subject to change without notice.

MHQ0603P6N2CT000



## Associated Images



! Images are for reference only and show exemplary products.  
! This PDF document was created based on the data listed on the TDK Corporation website.  
! All specifications are subject to change without notice.