

Style
M8 Socket, shielded
4 pin
A-coding

Ratings
Voltage: 30V
Current: 3A

Operating Temperature Range
-40~105 °C


Materials
① Insulator: PA66, UL 94 HB, black
② Pin: C3604 brass, gold flashing
③ Nut: C3604 brass, nickel plated
④ Shell: C3604 brass, nickel plated
⑤ O-ring: Silicone rubber
⑥ Epoxy: Epoxy resin

Electrical Requirements
Dielectric strength: 1 min @ 500 Vac
Insulation resistance: 100 MΩ @ 500 Vdc
Contact resistance: 10 mΩ or less

Mechanical Requirements
Life cycle: 1000 mating cycles minimum

Environmental Requirements
Salt spray test: 35 °C, relative humidity 90-95%, 5% NaCl mist for 24 hrs. Wash parts after test. Maintain mechanical requirements and a contact resistance of less than 10 mΩ.
Waterproof: IP67

Assembly Info
Wire gauge: 24 AWG max



Revision:	Date:	Description:
A	8/26/21	Initial Release

Prepared:
Verified:
Dimensions are in millimeters. Tolerances: X: ± 0.3 mm X.X: ± 0.1 mm X.XX: ± 0.05 mm

Notes: RoHS compliant Function test: no open, no short circuit, no intermittent
Description: Connector, M8 A-code socket, 4 pin, 8xL18.7 mm, panel mount, solder cup, gold plated, IP67

TENSILITY	
tel 1.541.323.3228 800 877.670.7118 fax 1.541.323.4202 web tensility.com	
Size: A	Part number: 54-00297
Scale: 2:1	Sheet 1 of 1