




**Part Number :** [622018810](#)

**Product Description :** Impact 85 Ohm Backplane Press-In Tool for 6-Pair by 16-Column Assemblies

**Series Number :** 207123

**Status :** Obsolete

**Product Category :** Application Tooling Accessories



---

## Documents & Resources

### Tooling Specifications

[ATS-622018810-001.pdf](#)

[TM-622018799-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Obsolete
Category	Application Tooling Accessories
Series	207123
Description	Impact 85 Ohm Backplane Press-In Tool for 6-Pair by 16-Column Assemblies
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	Impact
Tool Type	Press-Fit Insertion Tool
UPC	884982555426
Warranty Disclaimer	<p>CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.</p>

---

### Applicable Parts

Description	Part Number
Impact 85 Ohm Plus 6 Pair Vertical Backplane Header, Unguided, Open Endwalls, 16 Columns, 288 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead Free	<u>1705351607</u>

Impact 85 Ohm Plus 6 Pair Vertical Backplane Header, Unguided, Open Endwalls, 16 Columns, 288 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead Free	<u>1705351608</u>
Impact 85 Ohm Plus 6 Pair Vertical Backplane Header, Left Guided, Open Endwall, 16 Columns, 288 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead Free	<u>1705353607</u>
Impact 85 Ohm Plus 6 Pair Vertical Backplane Header, Left Guided, Open Endwall, 16 Columns, 288 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Polarizing Key Position C, Lead Free	<u>1705353637</u>
Impact 85 Ohm Plus 6 Pair Vertical Backplane Header, Right Guided, Open Endwall, 16 Columns, 288 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead Free	<u>1705355607</u>

---

This document was generated on Nov 09, 2024