


Subminiature DIL relays 2 A



Electronic
circuit boards



Hi-Fi systems



Printers



Toys






Medical and
dentistry



Hoists and
cranes



Door and
gate openers



Finder reserves the right to make changes to its products and their technical specifications at any time and without prior notice, as part of its policy of continuous improvement.
The information contained in this document is provided for indicative purposes only and does not constitute a contractual obligation; errors and omissions excepted.
In the event of any discrepancy between the printed and online versions, the latter, available at findernet.com, shall prevail.

Printed circuit mount



2 A signal relay

- 2 Pole changeover contacts Low level switching capability
- Subminiature - industry standard DIL package
- Sensitive DC coil - 200 mW
- Wash tight: RT III
- Cadmium Free contact material

30.22



- Low coil power
- Au clad contacts
- PCB mount



Copper side view

For outline drawing see page 5

Contact specification

Contact configuration		2 CO (DPDT)
Rated current/Maximum peak current	A	2/3
Rated voltage/ Maximum switching voltage	V AC	125/250
Rated load AC1	VA	125
Rated load AC15 (230 V AC)	VA	25
Single phase motor rating (230 V AC)	kW	—
Breaking capacity DC1: 24/110/220 V	A	2/0.3/—
Minimum switching load	mW (V/mA)	10 (0.1/10)
Standard contact material		AgNi + Au

Coil specification

Nominal voltage (U_N)	V AC (50/60 Hz)	—
	V DC	5 - 6 - 9 - 12 - 24 - 48
Rated power AC/DC	VA (50 Hz)/W	—/0.2
Operating range	AC	—
	DC	See table page 5
Holding voltage	AC/DC	—/0.35 U_N
Must drop-out voltage	AC/DC	—/0.05 U_N

Technical data

Mechanical life AC/DC	cycles	—/10 · 10 ⁶
Electrical life at rated load AC1	cycles	100 · 10 ³
Operate/release time	ms	6/4
Insulation between coil and contacts (1.2/50 μ s)	kV	1.5
Dielectric strength between open contacts	V AC	750
Ambient temperature range	°C	−40...+85
Environmental protection		RT III


Approvals (according to type)



Ordering information

Example: 30 series, PCB relay, 2 CO (DPDT) - 2 A contacts, 12 V sensitive DC coil.

A



Technical data

Insulation according to EN 61810-1

Nominal voltage of supply system	V AC	125/250
Rated insulation voltage	V AC	250
Pollution degrees		1

Insulation between coil and contact set

Type of insulation		Basic
Overvoltage category		I
Rated impulse voltage	kV (1.2/50 µs)	1.5
Dielectric strength	V AC	1000

Insulation between adjacent contacts

Type of insulation		Basic
Overvoltage category		I
Rated impulse voltage	kV (1.2/50 µs)	1.5
Dielectric strength	V AC	1500

Insulation between open contacts

Type of disconnection		Micro-disconnection
Dielectric strength	V AC/kV (1.2/50 µs)	750/1

Insulation between coil terminals


Rated impulse voltage (according to EN 61180)	kV (1.2/50 µs)	2
---	----------------	---

Other data

Bounce time: NO/NC	ms	2/6
Vibration resistance (10...38)Hz	g	10
Shock resistance	g	10
Power lost to the environment	without contact current W	0.2
	with rated current W	0.4
Recommended distance between relays mounted on PCB	mm	≥ 5

Contact specification

F 30 - Electrical life (AC1) v contact current (125 V)



Note:


The rated current of 2 A corresponds to the limiting continuous current.

Coil specifications

DC coil data - 0.2 W sensitive

Nominal voltage U_N	Coil code	Operating range		Resistance	Rated coil consumption
V		U_{min}	U_{max}	R	I at U_N
		V	V	Ω	mA
5	7.005	3.7	7.5	125	40
6	7.006	4.5	9	180	33
9	7.009	6.7	13.5	405	22
12	7.012	8.4	18	720	16
24	7.024	16.8	36	2880	8.3
48	7.048	33.6	72	11520	4.8

R 30 - DC coil operating range v ambient temperature



1 - Max. permitted coil voltage.

2 - Min. pick-up voltage with coil at ambient temperature.

Outline drawing

Type 30.22

