

This document is the property of Amphenol Corporation and is delivered on the express condition that is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.

The marking on this product doesn't contain environmental hazardous materials per Material Specification SS-00259 for Sony GP compliant or per directive 2011/65/EU for RoHS compliant.





ORIGINAL



REVISIONS				
SYM	ECN No.	DESCRIPTION	DATE	APPROVED
A	NE-16220	RELEASE TO PRODUCTION	09/26/2016	Arron Lin
B	NE-16278	ADDED RECOMMEND PANEL CUTOUT	12/07/2016	Arron Lin

NOTES:

1. MATERIAL:
HOUSING: THERMOPLASTIC , OPTIONS, UL94V-0, COLOR: OPTIONS.
USB 3.0 TERMINAL(5~9/14~18PIN): BRASS.
USB 2.0 TERMINAL(1~4/10~13PIN): PHOSPHOR BRONZE,
SHELL: STEEL
ISOLATED: SK7.
REAR SHELL: SK7
2. FINISH:
TERMINAL:
CONTACT AREA: SELECTIVE GOLD PLATING ;
SOLDERING AREA: MATTE-TIN PLATING 100 μ " THICKNESS MIN.;
UNDER PLATING: NICKEL PLATING 50 μ " THICKNESS MIN. OVERALL
SHELL:
NICKEL PLATING 50 μ " THICKNESS MIN. OVERALL
ISOLATED:
NICKEL PLATING 50 μ " THICKNESS MIN. OVERALL
REAR SHELL:
NICKEL PLATING 50 μ " THICKNESS MIN. OVERALL
4. THIS PRODUCT DOESN'T CONTAIN ENVIRONMENTAL HAZARDOUS PER DIRECTIVE 2011/65/EU FOR RoHS COMPLIANT.
5. PRODUCT SPECIFICATION REFER TO : PS-7425.



P/N: GSB3115 X X X F6HR


CONTACT FINISH:
1: FLASH GOLD
2: 15 μ " GOLD
3: 30 μ " GOLD

PACKING
T: TRAY
R: T&R

DIM L
1: 2.40
2: 3.30
3: 3.00

INSULATOR
7: PA4T (BLUE)
8: PA4T (BLACK)


RECOMMENDED P.C.B LAYOUT
TOLERANCE: ± 0.05 (TOP VIEWS)



TOLERANCE	APPROVALS	DATE	TITLE	
X.	DRAWN	Debby Hung	USB 3.0 TYPE A CONN. STACKED PORTS R/A SINK DIP TYPE W/O FLANGE (T/B)(CH=2.8H) SHELL DISTANCE 17.42mm	
X.X	CHECKED	Roger Tsai		
X.XX	APPROVED	Arron Lin		
X.XXX	DWG TYPE	CUST DWG		
ANGULAR $\pm 1^\circ$	PROJECT CODE	OTHER	UNIT	mm
UNLESS OTHERWISE SPECIFIED	SCALE	NA	SIZE	A3
	SHEET	1 OF 3	PART No.	GSB3115XXXXF6HR
	DWG No.	GSB3115XXXXF6HR	REV.	B

Amphenol®

Amphenol Corporation
Amphenol Taiwan Corporation





This document is the property of Amphenol Corporation and is delivered on the express condition that is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.

The marking on this product doesn't contain environmental hazardous materials per Material Specification SS-00259 for Sony GP compliant or per directive 2011/65/EU for RoHS compliant.





ORIGINAL




REVISIONS			
SYM	ECN No.	DESCRIPTION	DATE
A	NE-16220	RELEASE TO PRODUCTION	09/26/2016
B	NE-16278	ADDED RECOMMEND PANEL CUTOUT	12/07/2016



TRAY: L=350, W=250, H=21.5



PACKAGING BY TRAY	7.50	6.50	100	10	1000	GSB3115XXXTF6HR
	G/W KG	N/W KG	PCS/ TRAY	TRAYS/ BOX	QUANTITY (PCS)	PART NUMBER

TOLERANCE		APPROVALS		DATE	TITLE			Amphenol® Amphenol Corporation Amphenol Taiwan Corporation					
X.		DRAWN	Debby Hung	12/07/2016	USB 3.0 TYPE A CONN. STACKED PORTS R/A SINK DIP TYPE W/O FLANGE (T/B)(CH=2.8H) SHELL DISTANCE 17.42mm								
X.X	±0.30	CHECKED	Roger Tsai	12/07/2016									
X.XX	±0.20												
X.XXX	±0.10												
ANGULAR	±1°	APPROVED	Arron Lin	12/07/2016	UNIT	mm	SIZE	A3	PART No.	GSB3115XXXXF6HR			
UNLESS OTHERWISE SPECIFIED		DWG TYPE	CUST DWG	PROJECT CODE	OTHER	SCALE	NA	SHEET	2 OF 3	DWG No.	GSB3115XXXXF6HR	REV.	B



This document is the property of Amphenol Corporation and is delivered on the express condition that is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.

The marking on this product doesn't contain environmental hazardous materials per Material Specification 55-00259 for Sony GP compliant or per directive 2011/65/EU for RoHS compliant.

ORIGINAL




REVISIONS			
SYM	ECN No.	DESCRIPTION	DATE
A	NE-16220	RELEASE TO PRODUCTION	09/26/2016
B	NE-16278	ADDED RECOMMEND PANEL CUTOUT	12/07/2016



NOTES:

- MATERIAL:
CARRIER TAPE: PS.
COVER TAPE: PET.
REEL: PS.
SHIPPING BOX: CORRUGATED FIBERBOARD.
- DIMENSION:
REEL: $\phi = 330$.
SHIPPING BOX: L=350, W=350, H=315.
- PEELING STRENGTH: 0.1~1.3N(10~130 GRAMS)
- PEELING SPEED: 300mm/min.



PACKAGING BY T&R	6.18	4.68	120	6	720	GSB3115XXRF6HR
	G/W KG	N/W KG	PCS/ REEL	REELS/ BOX	QUANTITY (PCS)	PART NUMBER

TOLERANCE	APPROVALS	DATE	TITLE	UNIT	SIZE	PART No.
X. ±0.30	DRAWN Debby Hung	12/07/2016	USB 3.0 TYPE A CONN. STACKED PORTS R/A SINK DIP TYPE W/O FLANGE (T/B)(CH=2.8H) SHELL DISTANCE 17.42mm	mm	A3	GSB3115XXXXF6HR
X.X ±0.20	CHECKED Roger Tsai	12/07/2016				
X.XX ±0.10	APPROVED Arron Lin	12/07/2016				
ANGULAR ±1°	DWG TYPE CUST DWG	PROJECT CODE OTHER		SCALE NA	SHEET 3 OF 3	DWG No. GSB3115XXXXF6HR
UNLESS OTHERWISE SPECIFIED						REV. B

Amphenol®
Amphenol Corporation
Amphenol Taiwan Corporation

