HFA

1/4" x 1 1/4" in-line water-resistant fuse holder

RoHS



Product features

- For 1/4" x 1-1/4" (6.35 mm x 31.8 mm) fuses
- IP54 rating for exposed locations
- Accepts #16 to #12 copper wire
- Copper crimp lead material
- Recommended crimp tools:
  - Thomas & Betts – ERG4002
  - Channellock No. 909
  - Thomas & Betts WT-112M
- High temperature, flame retardant, phenolic meets UL 94 HB
- Crimp or 1/4" quick connect terminals
- In-line connection

Agency information

- UL Recognized: (IZLT2, E14853) HFA recognized with use of up to 12 AWG diameter wire secured with Thomas & Betts crimping tool WT-112M
- HFA-HH not UL Recognized

Ordering

- Specify packaging, product, and option code


General specifications

- Temperature Rating (RTI): +150 °C
- IP54 rating for exposed locations

SPECIFICATIONS			
Product code	Voltage rating	Current rating	Terminal
HFA	250 V	20 A	crimp
HFA-HH	250 V	20 A	1/4 Quick connect

Dimensions-inches

Drawing not to scale



Component	Material
Body	Phenolic
crimp	Copper, tin-plated

PACKAGING CODE	
Packaging Code	Description
Blank	10 pieces of fuseholders packed into a carton
BK	20 pieces of fuseholders packed into a carton

OPTION CODE	
Option Code	Description
-R	RoHS compliant version

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com/electronics

© 2020 Eaton
All Rights Reserved
Printed in USA
Publication No. 2115
September 2020

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

EATON
Powering Business Worldwide

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.