


PRODUCT NUMBER

PITCH

NFxx50x200J0G

5.08 mm








N=Number of poles
Dim A=Nx5.08
Dim B=(N-1)x5.08

Poles	Tolerance
2P-4P	±0.15
5P-8P	±0.20
9P-12P	±0.25
13P-15P	±0.30
16P-18P	±0.35
19P-24P	±0.40

PART NO.: NF xx 5 0 x 2 00J0 G

Solid block	0 Black (RAL9005)	RoHS compliant (lead<4%) In copper Alloy
No. of poles	2 Red (RAL3001/D)	
02 2 poles	3 Orange(RAL2011/P)	
03 3 poles	4 Yellow(RAL1018/A)	
...	5 Green(RAL6018/T)	
24 24 poles	6 Blue (RAL5015/A)	
	8 Grey(RAL7035/D)	
	9 White(RAL1102)	
	C Green(RAL6018/U)	





Material:

- Item①Top body:Thermoplastic (UL94V-0)
- Item②Bottom body:Thermoplastic(UL94V-0)
- Item③Spring clamp:Stainless Steel
- Item④Female contact: PhBz (CuSn) Tin plated
- Item⑤Lever:Thermoplastic(UL94V-0) Orange(RAL2011/P)
- Item⑥With left latch:Thermoplastic(UL94V-0)
- Item⑦With right latch:Thermoplastic(UL94V-0)

Electrical

- Voltage rating: 300VAC
- Current rating: 8A
- Solid wire: 12-26 AWG
- Stranded wire: 12-26AWG
- Wire strip length: 11-12mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval:

mat'l. code				surface ASME Y14.5		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK																	
ltr ecn no dr date				tolerances unless otherwise specified								title TERMINAL BLOCK SPRING CLAMP,PLUGGABLE PLUG,WITH LATCH															
				angles		X.±0.5																					
				linear		X.X±0.3		scale		dwg no NFxx50x200J0G																	
						X'±1°														X.XX±0.1							
				dr		EVIN ZHONG		052014		sheet 1 of 1 size A4																	
				engr		EVIN ZHONG		052014																			
				chr		HANKE FENG		052014																			
				appd		SHI JUN		052014																			
sheet index		revision sheet		A 1																							