

Part Number : 1731140387
Product Description : FCT Backshell Connector Kit, Black Plastic Backshell, Male Standard Density D-Sub Connector, 15 Circuits, Straight Cable Outlet, IP67 Waterproof
Series Number : 173114
Status : Active
Product Category : D-Sub Connector Kits
Engineering Part Number : FWH2-15P-3649

Documents and Resources

Drawings

1731140387_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant with Exemption 6(c); 6(a)-I per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	D-Sub Connector Kits
Series	173114
Description	FCT Backshell Connector Kit, Black Plastic Backshell, Male Standard Density D-Sub Connector, 15 Circuits, Straight Cable Outlet, IP67 Waterproof
Contact Type	Machined Solder
IP Rating	IP67
Magnetic	Yes
Product Name	FCT Products
Type	Plastic, Standard Density
UPC	191130516698

Electrical

Current - Maximum per Contact	7.5A
Shielded	No
Shield Type	None

Physical

Cable Diameter	6.00-8.00mm
Circuits (Loaded)	15
Circuits (maximum)	15
Color - Resin	Red, Black

Downloaded from Arrow.com.

Durability (mating cycles min)	500
Gender	Male
Material - Backshell	Polyester
Material - Contact	Brass
Material - Resin	Polybutylene Terephthalate (PBT)
Material - Screw	Brass
Material - Seal	Elastomer
Material - Shell	Brass
Mounting Style	Locking Screw
Net Weight	25.000/g
Number of Rows	2
Orientation	Straight
Packaging Type	Bag
Pitch - Mating Interface	2.84mm
Pitch - Termination Interface	2.84mm
Plating - Backshell	None
Plating - Contact	Gold over Nickel
Plating min - Mating	0.800µm
Plating min - Termination	0.100µm
Plating - Shell	Tin
Polarized to Mating Part	Yes
Ports	1
Shell Size	2
Temperature Range - Operating	-25° to +70°C
Termination Style	Solder Cup
Thread Size	4-40 UNC
Thread Type	Standard
Tightening Test Torque	40 Ncm
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP67
Wire Size (AWG)	20

Downloaded from Arrow.com.