



Have a Question?
Chat with a Product
Information Specialist



My Cart |



My Part Lists |



Sign In/Register



English (Change)

What can we help you find?



Products

Industries

Resources

About TE

My Account

Innovation

Support Center


Home > Products > Board-to-Board Connectors > Product Feature Selector > Product Details

828214-3 Product Details

Share

Print

Email



828214-3

TE Internal Number: 828214-3

Active

.100 inch AMPMODU Headers



Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector
- Header Type = Standard
- 3 Positions
- Mating Post Length = 6.70 mm
- Row-to-Row Spacing = 2.54 mm

[View all Features](#)

Quick Links

- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product



[Add to My Part List](#)



[Request Sample](#)



[Find Similar Products](#)



[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- AMPMODU II STIFTLISTE EINREIHIG (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- Product Line Information

Related Products:

- Tooling

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector
- Mount Angle = Vertical
- PCB Mount Retention = Without
- Surface Mount Compatible = No
- Board Standoff = Without
- Mating Connector Lock = Without
- Post Size (mm [in]) = 0.64 [.025]
- Profile = Standard

Mechanical Attachment:

- Mounting Ears = Without
- Panel Mount Retention = Without

Termination Features:

- Termination Post Length (mm [in]) = 3.20 [0.126]
- Solder Tail Contact Plating = Tin

Dimensions:

- Mating Post Length (mm [in]) = 6.70 [0.264]

Body Features:

- Header Type = Standard
- Row-to-Row Spacing (mm [in]) = 2.54 [0.100]
- Selectively Loaded = No
- Mount Type = Printed Circuit Board

Contact Features:

- Contact Plating, Mating Area, Material = Tin
- Contact Shape = Square
- Contact Base Material = Phosphor Bronze

Housing Features:

- Housing Material = Polyester
- UL Flammability Rating = UL 94V-0

Configuration Features:

- Number of Positions = 3
- Number of Rows = 1

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not reviewed for lead free solder process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- High Temperature Housing = No

Operation/Application:

- High Speed Serial Data Connector = No

Other:

- Brand = AMP

Corporate Information

[About TE](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

[Terms & Conditions](#)

[Privacy Policy](#)

Quick Links

[Distributor Inventory](#)

[Product Cross Reference](#)

[Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Knowledge Base](#)

[Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

