



Part Number : [2133530100](#)

Product Description : LTE/GPS Combo Flexible Antenna, 100.00mm Cable Length, Compatible with U.FL/I-PEX MHF Connectors

Series Number : 213353

Status : Active

Product Category : Antennas



Documents & Resources

Drawings

[2133530100_sd.pdf](#)

[2133530100-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[2133530100-001.pdf](#)

[2133530100-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Antennas
Series	213353
Description	LTE/GPS Combo Flexible Antenna, 100.00mm Cable Length, Compatible with U.FL/I-PEX MHF Connectors
Component Type	Flexible Antenna with Cable
Function	Signal
Product Name	LTE/GPS Combo Flexible Antenna
Protocol	BeiDou, Cellular, GLONASS, GPS, UWB
Type	Combo GPS/Cellular
UPC	193264456505

Electrical

Band_#10 F_End (MHz)	1606
Band_#10 F_Start (MHz)	1598
Band#1 F_End (MHz)	960
Band#1 F_Start (MHz)	698
Band#2 F_End (MHz)	1500
Band#2 F_Start (MHz)	1400

Band#3 F_End (MHz)	1700
Band#3 F_Start (MHz)	1500
Band#4 F_End (MHz)	2700
Band#4 F_Start (MHz)	1700
Band#5 F_End (MHz)	4200
Band#5 F_Start (MHz)	3300
Band#6 F_End (MHz)	5000
Band#6 F_Start (MHz)	4400
Band#7 F_End (MHz)	8500
Band#7 F_Start (MHz)	5900
Band#8 F_End (MHz)	1563
Band#8 F_Start (MHz)	1558
Band#9 F_End (MHz)	1576
Band#9 F_Start (MHz)	1573
Electrical Connectivity	Cable
Peak Gain (dBi)	2.3 @ 1400 MHz, 2.3 @ 1500 MHz, 2.5 @ 698 MHz, 4.5 @ 4400 MHz, 5.4 @ 1700 MHz, 5.4 @ 3300 MHz, 7.0 @ 5900 MHz
Return Loss - S11 (dB)	< -10, < -5
Total Efficiency	>45% @ 1558 MHz, >50% @ 1573 MHz, >50% @ 1598 MHz, >60% @ 1400 MHz, >60% @ 1500 MHz, >60% @ 1700 MHz, >60% @ 3300 MHz, >60% @ 4400 MHz

Physical

Cable Length	100.00mm
Length	119.40mm
Mounting Style	Adhesive
Net Weight	1.530/g
Packaging Type	PET Bag
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.10mm
Width	19.40mm

This document was generated on Sep 11, 2025