

Product data sheet

Specifications



Adaptor for T3 Type Circuit Breaker, 3 Pole

PD3PADAPT3

Overview

Lead time	Usually Ships within 6 Weeks
-----------	------------------------------

Main

Main Input Voltage	480 V 3 phases 400 V 3 phases
Main Output Voltage	480 V 3 phases
Output connector type	Hard wire 3-wire (3P) 1
Provided equipment	Installation guide Mounting hardware

Physical

Height	15.2 cm
Width	10.2 cm
Depth	7.6 cm
Net weight	1.59 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Not rack-mountable

Input

Network frequency	50 Hz 60 Hz
-------------------	----------------

Output

Max current draw	400 A
------------------	-------

Conformance

Product certifications	CE UL listed
------------------------	-----------------

Environmental

Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...40 °C

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	46.7 cm
Package 1 Width	19.4 cm
Package 1 Length	27.7 cm
Package 1 Weight	1.82 kg

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Under investigation

Use Again

 Repack and remanufacture	
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative



