







**CONNECTOR
DESIGNATORS
A-F-H-L-S
SELF-LOCKING
ROTATABLE
COUPLING**



STYLE 2
(See Note 3)



STYLE E
STRAIN RELIEF

311-039
Non Environmental Lamp-Base Thread EMI Adapter
with Strain Relief and Optional Shrink Boot
Self-Locking - Rotatable Coupling - Split Shell



311

See inside back cover fold-out or pages 13 and 14 for unabridged Tables I and II.

TABLE III: SPLIT 90° and SPLIT 45°					
SHELL SIZE		F	G	H	J
A-F-L-S	H	Max	Max	Max	Max
08	09	.596 (15.1)	1.740 (44.2)	.836 (21.2)	1.680 (42.7)
10	11	.656 (16.7)	1.800 (45.7)	.906 (23.0)	1.740 (44.2)
12	13	.716 (18.2)	1.870 (47.5)	.966 (24.5)	1.810 (46.0)
14	15	.776 (19.7)	1.900 (48.3)	1.026 (26.1)	1.840 (46.7)
16	17	.836 (21.2)	2.000 (50.8)	1.086 (27.6)	1.940 (49.3)
18	19	.906 (23.0)	2.060 (52.3)	1.156 (29.4)	2.000 (50.8)
20	21	.976 (24.8)	2.120 (53.8)	1.216 (30.9)	2.060 (52.3)
22	23	1.036 (26.3)	2.180 (55.4)	1.276 (32.4)	2.120 (53.8)
24	25	1.096 (27.8)	2.240 (56.9)	1.336 (33.9)	2.340 (59.4)

TABLE IV: ULTRA LOW-PROFILE SPLIT 90°					
SHELL SIZE		K	L	M	Max Wire
A-F-L-S	H	Ref.	Max	Max	Bundle
08	09	.496 (12.6)	2.020 (51.3)	.837 (21.3)	.250 (6.4)
10	11	.426 (10.8)	2.180 (55.4)	.887 (22.5)	.375 (9.5)
12	13	.426 (10.8)	2.180 (55.4)	.887 (22.5)	.375 (9.5)
14	15	.436 (11.1)	2.250 (57.2)	.987 (25.1)	.500 (12.7)
16	17	.576 (14.6)	2.300 (58.4)	1.137 (28.9)	.625 (15.9)
18	19	.796 (20.2)	2.330 (59.2)	1.337 (34.0)	.625 (15.9)
20	21	.796 (20.2)	2.330 (59.2)	1.337 (34.0)	.625 (15.9)
22	23	.696 (17.7)	2.480 (63.0)	1.337 (34.0)	.750 (19.1)
24	25	.696 (17.7)	2.480 (63.0)	1.337 (34.0)	.750 (19.1)

1. Cable Entry is defined as the accommodation range for the wire bundle or cable. Dimensions shown are not intended for inspection criteria.
2. Metric dimensions (mm) are indicated in parentheses.
3. When maximum entry (page 21) is exceeded, Style 2 will be supplied (not available for Function C). Dimensions F, G, H, & J will not apply. Please consult factory.
4. See Shrink Boot Reference Information (page 40).
5. Angular function "C", low-profile split elbow, not available with "S" connector designator.

TABLE V: CABLE ENTRY/SHRINK BOOT/DIMENSIONS					
Dash No.	N Max	P Max	Cable Entry Max	Shrink Boot	
01	.448 (11.4)	.781 (19.8)	.125 (3.2)	n/a	
02	.515 (13.1)	.968 (24.6)	.250 (6.4)	770-001S103	
03	.640 (16.3)	1.046 (26.6)	.375 (9.5)	770-001S103	
04	.765 (19.4)	1.156 (29.4)	.500 (12.7)	770-001S104	
05	.920 (23.4)	1.219 (31.0)	.625 (15.9)	770-001S104	
06	1.015 (25.8)	1.343 (34.1)	.750 (19.1)	770-001S105	
07	1.140 (29.0)	1.469 (37.3)	.875 (22.2)	770-001S106	
08	1.265 (32.1)	1.594 (40.5)	1.000 (25.4)	770-001S106	
09	1.432 (36.4)	1.719 (43.7)	1.125 (28.6)	770-001S107	
10	1.515 (38.5)	1.844 (46.8)	1.250 (31.8)	770-001S107	

TABLE II - STANDARD FINISHES

GLENAIR SYMBOL	FINISH
B	Cadmium Plate, Olive Drab
M	Electroless Nickel
NF	Cadmium Plate, Olive Drab Over Electroless Nickel

See Inside Back Cover for Complete Finish Information and Additional Finish Options