PSE Technology Corporation

SPECIFICATION FOR APPROVAL

CUSTOMER	
NOMINAL FREQUENCY	12.000000 MHz
HOLDER TYPE	TYPE FK 3.2x2.5 SEAM SEALED CRYSTAL CLOCK OSCILLATOR
SPEC. NO. (P/N)	FK1200011
CUSTOMER P/N	
ISSUE DATE	April 9, 2011
VERSION	C

APPROVED	PREPARED	QA
APPROVED BY CUSTOMER :		**AVL Status**
Please return one copy with approval to PSE-TW		

PSE Technology Corporation

No.2, Tzu-Chiang 5th Rd, Chung Li Industrial Park,
Chung Li City, Taoyuan County, Taiwan (R.O.C.)
TEL: 886-3-451-8888
FAX: 886-3-461-3865
http://www.saronix-ecera.com.tw

*Pb-free
*RoHS Compliant
*HF-Halogen Free
*REACH Compliant

*** *A company of PERICOM Semiconductor Corporation* ***

Downloaded from Arrow.com.

VERSION HISTORY

Version No.	Version Date	Customer Receipt Date	Supplier Receipt Date	Description	Notes
A	Apr.29,2009			Initial Release	
B	Jun.5,2009			Revised OE/OD function	
C	Apr.9,2011			Added Start up time: 10ms max & Updated Suggested IR Reflow Profile	

Downloaded from Arrow.com.

TYPE FK 3.2x2.5 SEAM SEALED CRYSTAL CLOCK OSCILLATOR

FK1200011

VER. C 9-Apr-11

ELECTRICAL SPECIFICATIONS

SRe Part Number : FK1200011

Item	Symbol	Specifications	Units	Notes
Nominal Frequency	Fo	12.000000	MHz	
Frequency Stability	FT	± 50	ppm	**See note
Operating Temperature Range	TR	-40 to +85	°C	
Supply Voltage	V_{DD}	+3.3 ± 5.0%	V	
Logic Type	LT	LVCMOS		
Supply Current, Output Enabled	I_{DD}/OE	10	mA	Max.
Supply Current, Output Disabled	I_{DD}/OD	10	µA	Max.
Duty Cycle (Symmetry)	DC/SY	45 / 55	%	Measured 50% of Waveform
Rise / Fall Time	T_R/T_F	5	ns	Max. measured 10/90% of Waveform
Output Voltage "0" Level	V_{OL}	10% V_{DD}	V	Max at I_{OL} = 4.0mA Min.
Output Voltage "1" Level	V_{OH}	90% V_{DD}	V	Min at I_{OH} = -4.0mA Max.
Output Load	CL	15	pF	Max.
Start Up Time		10	ms	Max.
Storage Temperature Range		-55°C to +125°C	°C	

※ This product doesn't include harmful substance that stipulated by SONY SS-00259 Level 1 and S-AT2-001 Level 1 standard. RoHS Compliant (Pb - Free).

****Stability includes all combinations of Operating Temperature, Load changes, rated Input (Supply) Voltage changes, Initial Calibration Tolerance (25°C), Aging (1 year at 25°C Average Effective Ambient Temperature), Shock and Vibration.**

Output Enable / Disable Function

Parameter	Min.	Typ.	Max.	Units	Notes
Input Voltage (Pin1), Output Enable	$0.7V_{DD}$			V	Or Open
Input Voltage (Pin1), Output Disable (low power standby)			$0.3V_{DD}$	V	Output is Hi-Z
Internal Pullup Resistance	30			KΩ	
Output Disable Delay			50	ns	

Downloaded from Arrow.com.

TEST CIRCUIT



OUTPUT WAVEFORM



Downloaded from Arrow.com.

RELIABILITY SPECIFICATIONS

ENVIRONMENTAL:

a) THERMAL SHOCK: MIL-STD-883, Method 1011, Condition A

b) MOISTURE RESISTANCE: MIL-STD-883, Method 1004

c) VIBRATION: MIL-STD-883, Method 2007, Condition A

d) RESISTANCE TO SOLDERING HEAT: J-STD-020D Table 5-2 Pb-free devices (except 2 cycles max)

e) HAZARDOUS SUBSTANCE: Pb - free and RoHS Compliant.

MECHANICAL:

a) SHOCK: MIL-STD-883, Method 2002, Condition B

b) SOLDERABILITY: JESD22-B102-D Method 2 (Preconditioning E)

c) TERMINAL STRENGTH: MIL-STD-883, Method 2004, Test Condition D

d) GROSS LEAK: MIL-STD-883, Method 1014, Condition C

e) FINE LEAK: MIL-STD-883, Method 1014, Condition A2, R1=2x10^{-8} atm cc/s

f) SOLVENT RESISTANCE: MIL-STD-202, Method 215

SUGGESTED IR REFLOW PROFILE

*As per IPC-JEDEC J-STD-020D



Note:

	Stage	Temperature	Time
A	Preheat	150~200°C	60~120 Sec
B	Primary Heat	217°C	60~150 Sec
C	Peak	260°C	10 Sec

For soldering reflow profile and reliability test ratings go to: http://www.pericom.com/pdf/sre/reflow.pdf

Downloaded from Arrow.com.

MARKING



MECHANICAL DRAWINGS (Scale: None. Dimensions are in mm.)



Recommended Land Pattern*



*External high-frequency power decoupling is recommended.(see test circuit for minimum recommendation). To ensure optimal performance, do not route traces beneath the package.

Pin	Function
1	OE
2	Ground
3	Clock Output
4	V_{DD}

Downloaded from Arrow.com.

TAPE&REEL





1. 230mm minimum leafer which consist of carrier and/or tape followed by a minimum of 160mm of empty carrier tape sealed with cover tape.
2. 160mm minimum trailer of empty carrier tape sealed with cover tape.

Downloaded from Arrow.com.

PACKING



3000pcs-Product Tape





Downloaded from Arrow.com.