

Tiny dual-band GNSS measurement engine module



Features

- Simultaneous multiconstellation and multi band L1 and L5 GNSS
- -162 dBm tracking sensitivity
- 1 m CEP position accuracy
- GNSS Raw measurement data (Carrier phase)
- Firmware upgrade and configuration
- Embed LNA and SAW
- Antenna monitor
- VCC/VBAT/VCC_IO supply voltage 3.3 V
- LCC 18 pin packages (9.7 mm x 10.1 mm)
- Operating temperature (from -40 °C to 85 °C)
- 12 µA standby current and 36 mA GNSS L1 and L5 current consumption

Description

The Teseo-LIV4FM module is an easy-to-use global navigation satellite system (GNSS) standalone measurement engine module, embedding Teseo IV single die standalone positioning receiver IC working simultaneously on multiple constellations (GPS/Galileo/Glonass/BeiDou/QZSS).

The Teseo-LIV4FM module brings the proven high quality GNSS measurement data, with that the customer can address precise positioning applications like micro mobility, agriculture, drone by achieving centimeter level accuracy using on the MCU-host RTK/PPP algorithm.

Within its 9.7x10.1 mm tiny size, Teseo-LIV4FM is offering superior accuracy thanks to the on-board temperature compensated crystal oscillator (TCXO) and a reduced Time To First Fix (TTFF) relying to its dedicated Real Time Clock (RTC) oscillator.

Teseo-LIV4FM module, being a certified solution, optimizes the time to market of the final applications with a temperature operating range from -40 °C to 85 °C.

Product status link

[Teseo-LIV4FM](#)

Product summary

Order code	Teseo-LIV4FM
Marking	Teseo-LIV4FM
Temperature range	-40 °C, 85 °C
Package	LCC-18 (9.7 mm x 10.1 mm)
Packing	Tape and reel



Revision history

Table 1. Document revision history

Date	Revision	Changes
04-Jul-2023	1	Initial release.

IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2023 STMicroelectronics – All rights reserved