



Part Number : [2204091011](#)
Product Description : Sentrality 6.00mm Right-Angle Pin, 12.85mm Engagement Length, Tray
Series Number : 220409
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

[2204091011_sd.pdf](#)
[2204161011-PK-000.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)
[Symbol and Footprint \(Multi-Format\)](#)

Specifications

[2204090000-AS-000.pdf](#)
[2204090000-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	220409
Description	Sentrality 6.00mm Right-Angle Pin, 12.85mm Engagement Length, Tray
Application	Board-to-Board, Busbar-to-Board, Power
Comments	Current and voltage performances are dependent upon application variables.
Component Type	PCB Header
Product Name	Sentrality
UPC	196823277702

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	140.0A
Voltage - Maximum	1000V

Physical

Breakaway	No
Circuits (Loaded)	1
Circuits (maximum)	1
Diameter	6.00mm
Durability (mating cycles max)	200
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Height Above Board	20.50mm
Material - Metal	Copper Alloy
Material - Plating Mating	Silver
Material - Plating Termination	Silver
Net Weight	27.330/g
Number of Rows	1
Orientation	Right Angle
Packaging Type	Tray
PCB Retention	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Pin-in-Paste SMT

Mates With / Use With

Mates with Part(s)

Description	Part Number
Sentrality Right-Angle Socket Assemblies	<u>220413</u>

This document was generated on Apr 21, 2026