





REVISION RECORD				
REV	ECO	DESCRIPTION	DRFT	CHKD
△		NOTES MODIFY	11/08/04	



PC BOARD LAYOUT COMPONENT SIDE SHOWN

NOTES:**ELECTRICAL:**

- VOLTAGE RATING : 125 VAC RMS.
- CURRENT RATING : 1.5 AMP.
- CONTACT RESISTANCE : 35 MILLIOHMS MAX.
- INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 500 VDC.
- DIELECTRIC STRENGTH : 1000 VAC RMS 60Hz, 1MIN.

MECHANICAL:

- HOUSING MATERIAL : FR52
- CONTACT MATERIAL : PHOSPHOR BRONZE t=0.35mm.
- △ 3. PLATING : GOLD PLATING OVER NICKEL.
- OPERATING LIFE : 750 CYCLES MIN.
- △ 5. PCB RETENTION POST-SOLDER: 10 LBS MIN.

ENVIRONMENTAL:

- STORAGE : -40°C TO +85°C.
 - △ 2. OPERATION: -40°C TO +85°C.
- MATES WITH MODULAR PLUG CONFORMING TO
FCC PART 68, SUBPART F.

PART NUMBER: E5388-EQ05QX-L

1- 3U" 2- 6U"
3- 15U" 4- 30U"
5- 50U"

DETACHED LISTS	MM (INCH)	DFTO SAMMY	DATE 06/08/04	FULL RISE ELECTRONIC CO., LTD	
	TOLERANCES EXCEPT AS NOTED	CHKD SAMMY	DATE 2004/11/16		
	MM	MFO	DATE	TITLE	
	.0 ±0.20	APPVLLUSHENG	DATE 2004/11/17	SIDE ENTRY 8P(LEAD_FREE)	
	.00 ±0.15			DRAWING NO. GE533095	
	.000 ±0.075			/PART NO. SEE NOTE	
	ANGLES ±	MATERIAL :		SIZE A3	
	THIRD ANGLE PROJECTION	QT'Y :		REV 1	
		FINISH :		DO NOT SCALE DRAWING	
		SCALE : 3:1		SHEET X OF Y	