


CGA3E2C0G1H102J080AD



TDK item description CGA3E2C0G1H102JT***B

Applications	Automotive Grade
Feature	AEC-Q200 Conductive Epoxy Application
Series	CGA3(1608) [EIA 0603]
Status	Production
Brand	TDK



Size	
Length(L)	1.60mm ±0.15mm
Width(W)	0.80mm ±0.15mm
Thickness(T)	0.80mm ±0.15mm
Terminal Width(B)	0.20mm Min.
Terminal Spacing(G)	0.30mm Min.
Recommended Land Pattern (PA)	0.70mm to 1.00mm
Recommended Land Pattern (PB)	0.80mm to 1.00mm
Recommended Land Pattern (PC)	0.60mm to 0.80mm

Electrical Characteristics	
Capacitance	1nF ±5%
Rated Voltage	50VDC
Temperature Characteristic	C0G(0±30ppm/°C)
Q (Min.)	1000
Insulation Resistance (Min.)	10000MΩ
Allowable Voltage	
Allowable Current	

Other	
Operating Temp. Range	-55 to 125°C
Soldering Method	Conductive Epoxy
AEC-Q200	YES
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	4000pcs

! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

CGA3E2C0G1H102J080AD



Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)

