


REV	DOCUMENT	CHANGED BY	CHECK
6	0038111	PK 20MAY08	ASD



RELEASE NO.	SR-10699
REPLACES	-

CHARACTERISTICS		ELECTRICAL DATA				DESIGN UNITS: INCH				DRAWN	VK	17OCT07		Honeywell				
OPERATING FORCE — — — — 3 - 5 OZ		CONTACT ARRANGEMENT S P D T				TOLERANCES UNLESS NOTED:				CHECK	RJ	17OCT07						
RELEASE FORCE— — — — 1 OZ MIN		30 VOLTS DC RATING				NO PLACE X ±				THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.				TITLE SWITCH - BASIC				
						ONE PLACE .X ± 0.030												
		SEA LEVEL 50,000 FT				TWO PLACE .XX ± 0.015												
						THREE PLACE .XXX ± 0.005												
DIFFERENTIAL TRAVEL— — — .004 MAX		INDUCTIVE	1/2 AMP	1/2 AMP		FOUR PLACE .XXXX ±				INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY				SIZE	TYPE	DRAWING NAME		REV
OVERTRAVEL — — — — — .003 MIN		RESISTIVE	1 AMP	1 AMP		ANGLES ±								B	I	12SM4 - T2		6
		MAXIMUM INRUSH 2 AMP				THIRD ANGLE PROJECTION				RASTER				SCALE	-	WEIGHT .006 LB MAX	SHEET	1 OF 1
		APPROVALS	KEMA, CE	1A, 250V ~ T85 1E4		CE												
			UL, CSA	1A, 125 VAC		BRAND	L 22											